

Actuator

71-
622.0/D

Distribution by
Rs-online



<https://rs-online.eao.com/p/71-622.0/D>

Your product:



71-622.0/D Actuator

MOUNTING

Mounting type: Panel mounting

ELECTRICAL CHARACTERISTICS

Switching voltage and switching current:	Switch rating AC cosφ 0,7 ... 0,8		
	gemäss EN IEC 60947-5-1		
	Voltage	250 VAC	
	Current	3 A	
	Switch rating DC		
	gemäss EN IEC 60947-5-1		
Surge voltage resistance:	Voltage	24 VDC	250 VDC
	Current	3 A	0.5 A
	2500 VAC, 50 Hz, 1 minute, as per DIN / IEC 60512-2 between all terminals and earth		
Recommended minimum operational data:	Voltage	5 VAC/DC	
	Current	10 mA	

MECHANICAL CHARACTERISTIC

Switching action:	Rest (a) - Maintained
Switching system:	Self-cleaning, double-break snap action switching system, 1 normally closed and 1 normally open contact per element.
Switching positions:	2 positions
Switching angle:	90° right
Mechanical lifetime:	50 000 cycles of operation
Tightening torque:	Fixing nut max. 0.5 Nm
Weight:	0.026 kg

AMBIENT CONDITION

IP Protection: IP65 front side


Operating temperature:	– 25 °C ... + 55 °C
Storage temperature:	– 40 °C ... + 85 °C
Shock resistance:	Max. 500 m/s ² , pulse width, 3-axis (sinusoidal EN IEC 60068-2-27)
Vibration resistance:	Max. 100 m / s ² from 10 Hz ... 500 Hz, (sinusoidal EN IEC 60068-2-6)
Climate resistance:	Damp heat, steady: 56 days, + 40 °C/93 % relative humidity, according to EN IEC 60068-2-78

CERTIFICATE

Conformities:	CE, UKCA, 2011 / 65 / EC (RoHS), 2014 / 35 / EU (LVD)
REACH:	REACH compliant
RoHS:	RoHS compliant

OTHER




Short Description:	Actuator, Rest (a) - Maintained
Housing material:	Plastic, according to UL 94 V0
Product attributes:	Standard lock: DOM 311
Hints:	Standard lock: DOM 311
Switching positions:	



Wiring diagrams:



Mounting cut-outs:



Dimension drawings:

