

product type designation

product description

Indoor fiber optic indoor cable

Glass fiber-optic cable, preferred length, preassembled

Indoor Fiber Optic (62.5/125), halogen-free, non-crush and flame-retardant fiber-optic internal cable pre-assembled with 4 BFOC connectors, length 75 m.



suitability for use

Non-crush, halogen-free and flame-retardant cable for indoor installation

version of the assembled FO cable

Assembled with four BFOC connectors

cable designation

I-V(ZN)HH 2x1 G 62,5/125 OM1

wire length

75 m

optical data

attenuation factor per length

- at 850 nm / maximum
- at 1300 nm / maximum

3 dB/km

0.8 dB/km

bandwidth length product

- at 850 nm
- at 1300 nm

300 GHz·m

800 GHz·m

mechanical data

number of fibers / per FOC core

1

number of FO cores / per FOC cable

2

version of the FO conductor fiber

Multimode graded-index fiber 62.5/125 µm, OM 1

design of the FOC core

Solid core, diameter 900 µm

design of the fiber-optic cable

Segmentable inner conductor

outer diameter

- of the optical fibers
- of the optical fiber sheath
- of the FOC core sheath

62.5 µm

125 µm

2.9 mm

symmetrical deviation / of the outer diameter of the FOC core sheath

0.1 mm

width / of cable sheath

6.8 mm

thickness / of cable sheath

3.9 mm

material

- of the fiber-optic cable core
- of the optical fiber sheath
- of the FOC core sheath
- of the fiber-optic cable sheath
- of the strain relief

Quartz glass

Quartz glass

FRNC

FRNC

Aramid fibers

color

- of the FOC core sheath
- of cable sheath

gray

orange

bending radius

- with single bend / minimum permissible
- with multiple bends / minimum permissible

30 mm

50 mm

tensile load

<ul style="list-style-type: none"> during installation / short-term 	800 N
<ul style="list-style-type: none"> during operation / maximum 	200 N
short-term shear force per length	300 N/cm
continuous shear force per length	100 N/cm
weight per length	30 kg/km
ambient conditions	
ambient temperature	
<ul style="list-style-type: none"> during operation 	-20 ... +60 °C
<ul style="list-style-type: none"> during storage 	-25 ... +70 °C
<ul style="list-style-type: none"> during transport 	-25 ... +70 °C
<ul style="list-style-type: none"> during installation 	-5 ... +50 °C
fire behavior	flame-resistant acc. to IEC 60332-1-2 and IEC 60332-3-22 (Cat. A)
chemical resistance	
<ul style="list-style-type: none"> to mineral oil 	acc. to IEC 60811-404 with test oil IRM 902 (acc. to ISO 1817), +70 °C, 4 h and +25 °C, 168 h
<ul style="list-style-type: none"> to grease 	not resistant
radiological resistance / to UV radiation	not resistant
protection class IP	IP20
product features, product functions, product components / general	
product feature	
<ul style="list-style-type: none"> halogen-free 	Yes
<ul style="list-style-type: none"> silicon-free 	Yes
product component / rodent protection	No
wire length	
<ul style="list-style-type: none"> for glass FOC / for 100BaseFX / for Industrial Ethernet / maximum 	4000 m
<ul style="list-style-type: none"> for glass FOC / for 1000BaseSX / for Industrial Ethernet / maximum 	500 m
<ul style="list-style-type: none"> for glass FOC / for 1000BaseLX / for Industrial Ethernet / maximum 	1000 m
<ul style="list-style-type: none"> for glass FOC / with PROFIBUS / maximum 	3000 m
standards, specifications, approvals	
certificate of suitability	
<ul style="list-style-type: none"> RoHS conformity 	Yes
reference code	
<ul style="list-style-type: none"> according to IEC 81346-2 	WH
<ul style="list-style-type: none"> according to IEC 81346-2:2019 	WHA
further information / internet links	
internet link	
<ul style="list-style-type: none"> to web page: selection aid TIA Selection Tool 	http://www.siemens.com/tia-selection-tool
<ul style="list-style-type: none"> to website: Industrial communication 	http://www.siemens.com/simatic-net
<ul style="list-style-type: none"> to website: Industry Mall 	https://mall.industry.siemens.com
<ul style="list-style-type: none"> to website: Information and Download Center 	http://www.siemens.com/industry/infocenter
<ul style="list-style-type: none"> to website: Selection guide for cables and connectors 	https://sie.ag/2QdlxcP
<ul style="list-style-type: none"> to website: Image database 	http://automation.siemens.com/bilddb
<ul style="list-style-type: none"> to website: CAX-Download-Manager 	http://www.siemens.com/cax
<ul style="list-style-type: none"> to website: Industry Online Support 	https://support.industry.siemens.com

last modified:

9/2/2023 