



Passive Components > Resistors > Fixed Resistors > Surface Mount Resistors



Resistor Type: **Precision Resistor**

Number of Terminations: **2**

Size Code: **0402**

Packaging Method: **Taped & Reeled**

Tolerance: **.1%**

## Features

### Product Type Features

Product Type	Fixed Resistor
Resistor Type	Precision Resistor
Size Code	0402

### Configuration Features

Number of Resistors	1
---------------------	---

### Electrical Characteristics

Voltage Rating	25 V
Tolerance	.1%
Resistance Range	1k $\Omega$ – 1M $\Omega$ $\Omega$
Resistance	3.74K $\Omega$
Power Rating	.063 W

### Termination Features

Number of Terminations	2
Termination Type	Solder

### Mechanical Attachment

Mount Style	Surface Mount
-------------	---------------

### Dimensions

Dimensions	1 x .5 x .3 mm
------------	----------------

### Usage Conditions



Temperature Coefficient	±25 ppm/°C
-------------------------	------------

### Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	欧洲化学品管理局最新发布的SvHCs候选清单: 2019年1月 (197) SvHCs候选清单的声明更新至: 2019年1月 (197)
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

### Compatible Parts



TE Part # 3-1879216-5  
CPF0402 200K 0.1%  
25PPM 1K RL



TE Part # 1-1614959-4  
CPF0805 2M0 0.1% 25PPM  
1K RL




TE Part # 1-1879417-9  
CPF 0603 1M0 0.1%  
25PPM 1K RL



TE Part # 1879417-8  
CPF0603 1M0 0.1% 25PPM  
5K RL

Also in the Series | **Neohm CPF**



Power Cable Assemblies(1)



Surface Mount Resistors  
(3022)

Customers Also Bought



TE Part #5-146128-2  
04 MODII HDR SR SFMNT  
B/A .100



TE Part #1879208-6  
CPF 0402 16R 0.1% 25PPM  
1K RL



TE Part #5-147278-1  
02 MTE HDR SRRA SFMNT  
.100CL



TE Part #3-1879215-9  
CPF 0402 10K5 0.1%  
25PPM 1K RL



TE Part #1825097-4  
TPB11CGRA204



TE Part #5-146130-5  
12 MODII HDR DRST  
SFMNT B/A LF



TE Part #4-1879213-2  
CPF 0402 69R8 0.1%  
25PPM 1K RL



TE Part #6-534267-2  
30 MODIV VRT DR DE 100  
/125

Documents

Product Drawings

CPF 0402 3K74 0.1% 25PPM 1K RL

English

CAD Files

3D PDF

3D



Customer View Model

[ENG\\_CVM\\_CVM\\_9-1879214-7\\_BA.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_9-1879214-7\\_BA.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_9-1879214-7\\_BA.3d\\_stp.zip](#)

English

---

**Datasheets & Catalog Pages**

[1309350\\_PASSIVE\\_COMPONENT](#)

English

[CPF-1016](#)

English

[8-1773459-4\\_POWER\\_FILTERING\\_AND\\_RESISTIVE\\_SOLUTIONS\\_FOR\\_ELEVATORS\\_AND\\_ESCALATORS](#)

English