



Technical data

NJ2316

Single row cylindrical roller bearings

Single row cylindrical roller bearing, single direction for axial loads, separable, pressed steel cage.

VISUAL (S)



PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	80 mm
D - External diameter	170 mm
B - Bearing/Inner ring width	58 mm
E - Upper roller diameter	147 mm
F - Under roller diameter	103 mm
d1 - IR flange outer diameter	111,8 mm
rs - Min fillet radius	2,1 mm
r1s - Min fillet radius	2,1 mm
Radial clearance class	CN
Mass	6,13 kg

PRODUCT PERFORMANCE

C - Dynamic load	305000000 mN
C0 - Static load	330000000 mN
Cu - Fatigue limit load	38000000 mN
N lim - Oil lubrication limit speed	25200 °/s
N lim - Grease lubrication limit speed	21600 °/s
Tmin - Min operating temperature	233,15 °K
Tmax - Max operating temperature	393,15 °K

ABUTMENT

da min - Min shoulder diameter IR	91 mm
da max - Small face shoulder max diameter	99 mm
dc min - Min inner ring GO diameter	114 mm



ABUTMENT	
Da max - Max shoulder diameter OR	159 mm
ra max - Max fillet radius	2 mm

INDUSTRY CALCUL FACTORS	
Equivalent dynamic radial load	
$P = Fr$	
Equivalent static radial load	
$P_0 = Fr$	