



Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided equipment	Rack mounting brackets User manual Warranty card
--------------------	--

Physical

Colour	Black
Depth	59.4 cm
Height	8.5 cm
Net weight	40.6 kg
Number of rack unit	2U
Width	43.2 cm

Conformance

Standards	OSHPD
-----------	-------

Environmental

Ambient air temperature for operation	0...40 °C
Operating altitude	0...10000 ft
Relative humidity	0...95 % non-condensing
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.00...15240.00 m

Batteries & Runtime

Number of battery free slots	0
Number of battery filled slots	0

Battery voltage	96 V
Battery type	Lead-acid battery
Number of battery replacement quantity	2

Packing Units

Package 1 Weight	44.5 kg
Package 1 Height	23.9 cm
Package 1 width	59.9 cm
Package 1 Length	83.1 cm
Number of Units in Package 3	6

Offer Sustainability

Sustainable offer status	Green Premium product
RECh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------