

Rotary hammer XGT®

HR006G

40V max X2 • SDS-MAX • 52 mm • 21.4 J

Powerful BL motor is suitable for handling the most demanding applications.

Constant speed control automatically applies additional power to the motor to maintain speed under load to complete the most challenging jobs. Twin LED lights with preglow and afterglow functions for better illumination.



Technical specifications

Nominal Battery Voltage	2 x 40 V
Voltage XGT	✓
Brushless Motor	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	150 - 310 min ⁻¹
Impacts per Minute (IPM)	1100 - 2250 min ⁻¹
Max. Drilling Diameter in Concrete	52 mm
Optimum Drilling Diameter Range in Concrete	25 - 45 mm
Impact Energy	21,4 J
Drilling diameter with TCT core bit	160 mm
Adapted for SDS-MAX bits	✓
Electronic brake	✓
AWS ready	✓
Sound Power Level (L _{WA})	109 dB(A)

User benefits

- Active Feedback sensing Technology (AFT) stops the engine if the rotation suddenly stops
- AVT (Anti-Vibration Technology) ensures extra-low vibration performance
- Auto-start Wireless System (AWS) connects to compatible vacuum cleaners with Bluetooth
- Twin LED lights with pre-glow and afterglow functions for better illumination and more accurate work
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Depth gauge for increased drilling consistency
- Torque limiting clutch engineered to minimises gear damage by automatically disengaging gears if the bit binds
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makita.uk.com



Related products

Optional AC

198993-4

Grease vessel for bit 100 ml



199143-4

Dust Extraction Attachment



199144-2

Dust Extraction Attachment



D-33978

T.C.T Drill Bit 20 x 200 / 340 mm,

D-33984

T.C.T Drill Bit 20 x 400 / 540 mm,

D-33990

T.C.T Drill Bit 22 x 200 / 340 mm,

D-34001

T.C.T Drill Bit 22 x 400 / 540 mm,

D-34017

T.C.T Drill Bit 24 x 200 / 340 mm,

D-34023

T.C.T Drill Bit 24 x 400 / 540 mm,

D-34039

T.C.T Drill Bit 25 x 200 / 340 mm,

D-34045

T.C.T Drill Bit 25 x 400 / 540 mm,

D-34051

T.C.T Drill Bit 28 x 250 / 370 mm,

D-34067

T.C.T Drill Bit 28 x 450 / 570 mm,

D-34073

T.C.T Drill Bit 30 x 250 / 370 mm,

D-34089

T.C.T Drill Bit 30 x 450 / 570 mm,

D-34095

T.C.T Drill Bit 32 x 250 / 370 mm,

D-34104

T.C.T Drill Bit 32 x 450 / 570 mm,

D-34110

T.C.T Drill Bit 35 x 250 / 370 mm,

D-34126

T.C.T Drill Bit 35 x 450 / 570 mm,

D-34132

T.C.T Drill Bit 38 x 250 / 370 mm,

D-34148

T.C.T Drill Bit 38 x 450 / 570 mm,

D-34154

T.C.T Drill Bit 40 x 250 / 370 mm,

D-34160

T.C.T Drill Bit 40 x 450 / 570 mm,

D-34207

Cold chisel SDS-MAX, 25 x 300 mm



D-34213

Cold chisel SDS-MAX, 25 x 400 mm

D-34229

Cold chisel SDS-MAX, 25 x 600 mm



D-34235

Scaling Chisel SDS-MAX 50 x 400



D-34241

Scaling Chisel SDS-MAX 80 x 300



Other

User manual

Parts drawing