



# Datasheet RS PRO Piezo Audio Indicator EN RS Stock No: 181-2740



### A. SCOPE

This specification applies piezo audio indicator, 1812697


#### **B. SPECIFICATION**

| No. | ltem                                      | Unit  | Specification                           |                | Condition                          |                                  |
|-----|---|-------|---|----------------|------------------------------------|----------------------------------|
| 1   | Resonant frequency                        | KHz   | 2.9 ± 0.5                               |                |                                    |                                  |
| 2   | Operating Volt.<br>range                  | VDC   | 7 ~ 18                                  |                |                                    |                                  |
| 3   | Current consumption                       | mA    | MAX 8<br>MAX                            | MAX 32<br>X 16 | at 7VDC at 12                      | at 18VDC<br>VDC                  |
| 4   | Sound pressure<br>level                   | dB    | MIN 80<br>MIN                           | MIN 95         | at 60cm/8VDC<br>at 60cm            | at 60cm/18VDC<br>/12VDC          |
| 5   | Rated Voltage                             | VDC   | 1                                       |                |                                    |                                  |
| 6   | Ton                                       |       | Slow Pulse (1.2Hz±20%)                  |                | at 12VDC                           |                                  |
| 7   | Operating temp.                           | °C    | -30 ~                                   | +85            |                                    |                                  |
| 8   | Storage temp.                             | °C    | -40 ~                                   | +85            |                                    |                                  |
| 9   | Dimension                                 | mm    | φ 42.5 x H32.5                          |                | See appearance drawing<br>請參照外觀尺寸圖 |                                  |
| 10  | Weight (MAX)                              | gram  | 36                                      | .0             |                                    |                                  |
| 11  | Material                                  |       | NYLON (BLACK)                           |                |                                    |                                  |
| 12  | Terminal                                  |       | Tin-Plated Tapped Screw<br>(Plating Sn) |                | See appearance drawing             |                                  |
| 13  | Environmental<br>Protection<br>Regulation |       | RoH                                     | S 2.0          |                                    |                                  |
| 14  | Storage life                              | month | 6                                       |                | 6 months preserva<br>(25±3℃), H    | tion at room temp.<br>umidity40% |






## C. APPEARANCE DRAWING



#### Tol: ± 0.5 Unit: mm D. MEASURING METHOD

S.P.L. Measuring Circuit



Mic : RION S.P.L meter UC30 or equivalent





### **E. MECHANICAL CHARACTERISTICS**

| No. | ltem                               | Test Condition   | <b>Evaluation standard</b>   |  |
|-----|------------------------------------|--|--|--|
| 1   | Solderability                      | Lead terminals are immersed in rosin for 5 seconds and then immersed in solder bath of +270 $\pm$ 5°C for 3 $\pm$ 1 seconds.   | 90% min. lead terminals<br>shall be wet with solder.<br>(Except the edge of<br>terminal)         |  |
| 2   | Soldering Heat<br>Resistance       | Lead terminal are immersed up to 1.5mm from sounder's body in solder bath of $+300\pm5^{\circ}$ for $3\pm 0.5$ seconds or $+260\pm5^{\circ}$ for $10\pm1$ seconds.           | No interference in operation   |  |
| 3   | Terminal<br>Mechanical<br>Strength | The force 10 seconds of 9.8N (1.0kg) is applied to each terminal in axial direction.   | No damage and<br>cutting off   |  |
| 4   | Vibration                          | Buzzer shall be measured after being applied vibration of amplitude of 1.5mm with 10 to 55hz band of vibration frequency to each of 3 per-pendicular directions for 2 hours. | The value of oscillation<br>frequency/ current<br>consumption should be in<br>±10% compared with |  |
| 5   | Drop test                          | The part only shall be dropped from a height of 75cm onto a<br>40mm thick wooden board 3 times in 3 axes (X.Y.Z). (a total<br>of 9 times).                                   | initial ones .The SPL  |  |

### F. ENVIRONMENT TEST

| No. | ltem             | Test Condition  | Evaluation standard |
|-----|------------------|---|---------------------|
| 1   | High temp. test  | After being placed in a chamber at +85 $^\circ\!\mathrm{C}$ for 240 hours                             |                     |
| 2   | Low temp. test   | After being placed in a chamber at –40 $^\circ \! \mathbb{C}$ for 240 hours                           |                     |
| 3   | Humidity test    | After being placed in a chamber at +40 $^\circ\!\mathrm{C}$ and 90±5% relative humidity for 240 hours |                     |
| 4   | Temp. cycle test | +85°C<br>+25°C<br>+25°C   |                     |





### **G. RELIABILITY TEST**

| No. | Item                   | Test condition   | Evaluation   |
|-----|------------------------|--|--|
| 1   | Operating<br>life test | <ol> <li>Continuous life test</li> <li>250 hours continuous operation at +85°C with rated voltage applied.</li> <li>Intermittent life test         <ul> <li>A duty cycle of 1 minute on, 5 minutes off, a minimum of 10000 times at room temp.(+25±2°C) and rated voltage applied</li> </ul> </li> </ol> | Being placed for 4 hours at<br>+25°C, buzzer shall be<br>measured. The value of<br>oscillation frequency/<br>current consumption should<br>be in ±10% compared with<br>initial ones .The SPL should<br>be in ±10dB compared with<br>initial one. |

#### TEST CONDITION.

| Standard Test Condition:  | a) Temperature : +5 ~ +35 $^\circ$ C b) Humidity : 45-85% | c) Pressure : 860-1060mbar |
|---------------------------|---|----------------------------|
| Judgement Test Condition: | a) Temperature : +25 $\pm$ 2°C b) Humidity : 60-70%       | c) Pressure : 860-1060mbar |



