



**FAG****61910-2RZ**

Deep groove ball bearing

Deep groove ball bearing 619...-2RZ, single row, shields, steel sheet metal cage

Technical information



Your current product variant

Sealing	2RZ	Non-contact seal on both sides
Cage	JN	Steel sheet metal
Tolerance class	PN	Normal (PN)
Dimensional / heat stabilization	SN	Rings dimensional stabilized up to 120°
Lubricant	GA13	Ball bearing and insert bearing grease, standard for D>62mm
Radial internal clearance	CN (Group N)	Normal internal clearance
Bore type	Z	Cylindrical

Main Dimensions & Performance Data

d	50 mm	Bore diameter
D	72 mm	Outside diameter
B	12 mm	Width
C _r	15,400 N	Basic dynamic load rating, radial
C _{0r}	11,700 N	Basic static load rating, radial
C _{ur}	700 N	Fatigue load limit, radial
n _G	11,400 1/min	Limiting speed
n _{gr}	8,100 1/min	Reference speed
m	0.13 kg	Weight



Mounting dimensions

$d_{a\min}$	53.2 mm	Minimum diameter shaft shoulder
$D_{a\max}$	68.8 mm	Maximum diameter of housing shoulder
$r_{a\max}$	0.6 mm	Maximum fillet radius

Dimensions

r_{\min}	0.6 mm	Minimum chamfer dimension
D_1	65.24 mm	Shoulder diameter outer ring
D_2	67.3 mm	Caliber diameter outer ring
d_1	56.9 mm	Shoulder diameter inner ring

Temperature range

T_{\min}	-20 °C	Operating temperature min.
T_{\max}	100 °C	Operating temperature max.

Calculation factors

f_0	16.1	Calculation factor
-------	------	--------------------

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Lifetime lubrication, freedom from maintenance
	Grease Lubrication
	Sealed on both sides