

PSEN sc L 5.5 08-12

6D000013



Light model, 30 mm/40 mm/50 mm/70 mm/150 mm detection capability, muting, override, EDM, restart applications in accordance with EN ISO61496-3, vertical applications, reference markers, measurement data output (UDP), rapid exchange by exchangeable memory block; 5.5 m safety zone; max. 2 safety zones parallel active, max. 2 warning zones parallel active, max. 10 configurable zone sets.

## Technical details

General data	
Approval:	CE, cULus Listed, TÜV
ESPE type:	3
:	2
Product type:	Light
Sensor principle:	optisch
Selectable resolutions:	50, 40, 30, 150, 70
Range warning zone var. res.:	40 m/Auflösung 150 mm, 22 m/Auflösung 40 mm, 19 m/Auflösung 30 mm, 23 m/Auflösung 50 mm, 40 m/Auflösung 70 mm
Range safety zone various res.:	3 m/Auflösung 40 mm, 5,5 m/Auflösung 150 mm, 2,50 m/Auflösung 30 mm, 4 m/Auflösung 50 mm, 5,5 m/Auflösung 70 mm
Number of zone configurations:	10
Technical data	
Electrical data	
Supply voltage (V):	24 - 24 V
Type of supply voltage U1:	DC
Power consumption DC:	8
Optical data	
Used wavelength range:	905 nm
Scanning area:	275°
Max. opening angle vertical:	0,12°

Angular resolution:	0,1°
Inputs	
Signal level at input at 0:	< 5 V
DC voltage at input:	24 V
Semiconductor outputs	
Number of OSSD outputs:	4
Current "0" S/C O PSENscan:	< 700 µA
Ethernet interface	
Connector type ETHERNET int.:	M12x1, 4-pin, D-code
Ethernet transmission rate:	100 MBit/s
CANopen interface	
Number of Ethernet interfaces:	1
Environmental data	
Ambient temperature:	-10 - 50 °C
Humidity rating:	Max. 95 %
Condensation permitted?:	Not permitted
Perm. operating height ASL:	2000 m
Vibration to standard ...:	EN 60068-2-6
Acc. shock to standard1:	10g
Protection type, housing:	IP65
Times	
Reaction time:	62
Rotation time:	30
Mechanical data	
Connection type:	M12, 8pol. male, M12, 12pol. male
Housing material:	Aluminium
Housing material upper part:	PC
Material front screen:	PMMA
Height dimension:	152

Width dimension:	102
Depth dimension:	112.5
Net weight:	1530
Gross weight:	2140
Environment	
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
ECLASS version:	ECLASS-9.1
ECLASS Reference Feature:	27272791
ETIM Version:	ETIM-7.0

## Obligatory accessories



540326

PSEN cable axial M12 8-pole 30m



540320

PSEN cable axial M12 8-pole 5m



6D000011

PSEN sc bracket C



540321

PSEN cable axial M12 8-pole 10m



6D000010

PSEN sc bracket F



570356

PSEN cable M12-12sf 50m



570354

PSEN cable M12-12sf 20m



570355

PSEN cable M12-12sf 30m



570352

PSEN cable M12-12sf 5m



570353

PSEN cable M12-12sf 10m



540319

PSEN cable axial M12 8-pole 3m



570350

PSEN cable M12-12sf 2m



570351

PSEN cable M12-12sf 3m



631073

PSEN op Ethernet cable 10m



6D000004

PSEN sc bracket H



6D000002

PSEN sc bracket PR



6D000003

PSEN sc bracket P



631072

PSEN op Ethernet cable 3m



631071

PSEN op Ethernet cable 1m

## Optional accessories



6D000008

PSEN sc cleaner



6D000009

PSEN sc cloth



6D000006

PSEN sc memory 08-12



6D000007

PSEN sc head