

Parker Product Datasheet



Available in five sizes, SciPres™ scalable pressure sensors are designed for incorporation into single-use purification platforms. Pre-calibrated and gamma stable, calibration and identity information is stored on the sensor's chip.

PART NUMBER: 080-695PSX-5
CONNECTION TYPE: 1/2" Barb
MAXIMUM FLOW RATE: 17 LPM
OPTIONS: Non-Gamma
CALIBRATION TYPE: 2-pt (0-30psi)
TUBE SIZE RANGE: ID 0.50

PRODUCT OVERVIEW

The SciPres™ combines pressure sensing capabilities and the convenience of disposability with easy set up. Each sensor is pre-programmed with a unique ID for easy traceability and data documentation when combined with the SciLog® SciDoc software. Factory calibration data is also stored on each sensor's chip for out-of-box plug and play use.

Features & Benefits

- Each sensor is pre-calibrated and has a unique sensor ID making it NIST traceable and suitable for single-use GMP applications
- Validated for exposure to gamma irradiation, autoclave and sodium hydroxide sterilization
- Available in 5 different sizes for full scalability throughout process development

Careful monitoring and control of pressure is essential for the efficiency and safety of several units of operation within a biopharmaceutical manufacturing process. SciPres pressure sensors can measure and document pressure in a range of filtration, separation and purification applications, for example:

- Trans-membrane pressure (TMP) control in tangential flow/cross flow filtration operations is crucial in optimizing product yields.
- Critical normal flow filtrations such as virus filtration, final sterilizing filtration or mycoplasma removal from cell culture media are validated in the process to remove micro-organisms at a given differential pressure (dP) which must be maintained.
- Cross-column pressure measurement in chromatography operations monitors blockage preventing column or resin damage.
- The pressure across a centrifuge can be used as an indication of unit throughput.
- Monitoring pressure can also prevent a system integrity breach protecting operators from potential exposure to potent molecules or acids and bases.

TECH SPECIFICATIONS

DIVISION	Bioscience and Water Filtration Division
DIVISION	Bioscience and Water Filtration Division
INDUSTRY	Pharmaceuticals
SPECIFICATIONS MET	FDA 21 CFR 177.1520
SPECIFICATIONS MET	USP Class VI
APPLICATION	Pressure Sensing
BRAND	Parker
PRODUCT SERIES	SciPres Pressure Sensors
PRODUCT TYPE	Single-Use Sensors and Monitors
MATERIALS OF CONSTRUCTION	Medical Grade Polysulfone
OPERATING PRESSURE	-5 to 60 psi

WETTED MATERIAL

Animal-Free Compounds

ACCURACY

2-pt. calibration: ± 0.3 psi, 0 to 30 range (accuracy values define the maximum expected)

ACCURACY

3-pt. calibration: ± 0.3 psi, 0 to 60 range