

This document was generated on 01/21/2015 PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:	<u>43045-1209</u>		\sim
Status:	Active		
Overview:	Micro-Fit 3.0 [™] Connectors		
Description:		ce Mount, Dual Row, Right Angle, with Solder Tab, 12	
2000.1010	Circuits, Tin (Sn) Plating, Glo		
Documents:			
		Test Summer (TS 12015 001 (DDE)	
Drawing (PDF)		Test Summary TS-43045-001 (PDF)	
<u>3D Model</u> Braduct Specification		RoHS Certificate of Compliance (PDF)	Sorios
Product Specification	<u>1 PS-43045 (PDF)</u>	Product Literature (PDF)	Series
			image - Reference only
Agency Certification			
CSA		LR19980	EU RoHS China RoHS
TUV		R72081037	ELV and RoHS
UL		E29179	Compliant
			REACH SVHC
General			Not Reviewed
Product Family		PCB Headers	Low-Halogen Status
Series		<u>43045</u>	Low-Halogen
Application		Power, Wire-to-Board	Need more information on an advet
Comments		"High Temperature Square Pin Solder Type <p><p>This</p></p>	Need more information on product
		Molex product is manufactured from material that has	environmental compliance?
		the following ratings, tested by independent agencies:.	Email productcompliance@molex.com
		a) A Glow Wire Ignition Temperature (GWIT) of at	For a multiple part number RoHS Certificate of
		least 775 deg C per IEC 60695-2-13 b) A Glow	Compliance, <u>click here</u>
		Wire Flammability Index (GWFI) above 850 deg C	
		per IEC 60695-2-12.and hence complies with the	Please visit the Contact Us section for any
		requirements set out in the International Standard IEC	non-product compliance questions.
		60335-1 5th edition - household and similar electrical	····· [·······························
		appliances - safety, section 30 Resistance to heat	
		and fire. <p><p> The customers using this product</p></p>	Search Parts in this Series
		must determine its suitability for use in their particular	
		application through testing or other acceptable means	43045Series
		as described in end-product glow-wire flammability test	
		standard IEC 60695-2-11 and any applicable product	Mates With
		end-use standard(s). <p> If it is determined during</p>	<u>43025</u> Micro-Fit 3.0 [™] Receptacle Housing
		the customer's evaluation of suitability, that higher	· · · · · · · · · · · · · · · · · · ·
		performance is required, please contact Molex for	
		possible product options."	
Overview		Micro-Fit 3.0 [™] Connectors	
Product Literature Order No		987650-5984	
Product Name		Micro-Fit 3.0™	
UPC		800754372961	
Dhuclast			
Physical			
Breakaway		No	
Circuits (Loaded)		12	
Circuits (maximum)		12	
Color - Resin		Black	
Durability (mating cycles max)		30	
Flammability		94V-0	
Glow-Wire Complian	t	Yes	
Mated Height		10.29mm	
Material - Metal		Brass	
Material - Plating Ma	ting	Tin	
Material - Plating Termination		Tin	
		••••	

Material - Resin	High Temperature Thermoplastic		
Net Weight	1.877/g		
Number of Rows	2		
Orientation	Right Angle		
PCB Locator	Yes		
PCB Retention	Yes		
PCB Thickness - Recommended	1.60mm		
Packaging Type	Embossed Tape on Reel		
Pitch - Mating Interface	3.00mm		
Plating min - Mating	0.254µm		
Polarized to PCB	Yes		
Shrouded	Fully		
Stackable	No		
Surface Mount Compatible (SMC)	N/A		
Temperature Range - Operating	-40°C to +105°C		
Termination Interface: Style	Surface Mount		
Electrical			
Current - Maximum per Contact	5A		
Voltage - Maximum	600V		
Ŭ			
Solder Process Data			
Duration at Max. Process Temperature (seconds)	30		
Lead-free Process Capability	Reflow Capable (SMT only)		
Max. Cycles at Max. Process Temperature	3		
Process Temperature max. C	260		
Material Info			
Reference - Drawing Numbers			
Product Specification	PS-43045, RPS-43045-003, RPS-43045-004		
Sales Drawing	SD-43045-004		
Test Summary	TS-43045-001		
, · · ·			

This document was generated on 01/21/2015 PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION