

Impact Wrench LXT®

DTW180

18V • 3/8" • 180 Nm • 0 – 2 400 min⁻¹

An extra-compact and efficient brushless impact wrench for tight spaces with two power settings

A compact, brushless 3/8" impact wrench. Small size and light weight make this tool easy to use, while offering a max. fastening torque of 180 Nm. Two power settings. Automatic stop of rotation in 0,2 seconds once the bolt is loose. Equipped with an LED light.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Max Fastening Torque Impact Drill	65 / 180 Nm
No load speed	0 - 1300 / 2400 min ⁻¹
Impacts per Minute (IPM)	0 - 2000 / 3600 min ⁻¹
Drive Square	3/8 "
Tightening Capacity Standard Bolt	M8 - M16
Sound Power Level (L _{WA})	100 dB(A)
Sound Pressure Level (L _{pA})	92 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	1,2 - 1,5 kg
Product Dimensions (L x W x H):	144 x 79 x 235 mm
Brushless Motor	✓
Nut-busting torque	310 Nm
Battery Chemistry (Ni-Cd / Ni-MH / Li-	Li-ion

User benefits

- Brushless maintenance-free and long-life motor
- The rubber coating on the handle ensures a firm working grip
- LED light illuminates the work site
- Electric brake for maximum productivity and increased operator safety
- Variable 2-speed options allows the user to match speed to application
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Battery protection circuit protects against overloading, over-discharging and over-heating

Link to product - www.makitauk.com



Related products

■ Optional AC

821550-0
Makpac case (2)



837670-0
MakPac (2) Inlay



■ Other

User manual

Parts drawing