



Connectors > Connector Accessories > Connector Caps & Covers > Pin Connector: Strain Relief, Universal



Connector Cover Type: **Strain Relief Cover**
Primary Product Color: **Black**
Primary Product Material: **Glass-Filled Polyester**

[All Pin Connector: Strain Relief, Universal \(12\)](#)

Features

Product Type Features

Connector Cover Type	Strain Relief Cover
----------------------	---------------------

Body Features

Primary Product Color	Black
Primary Product Material	Glass-Filled Polyester

Dimensions

	1.44 in
--	---------

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
Compatible With Approved Standards Products	CSA LR7189, UL E28476

Packaging Features

Packaging Method	Package
Packaging Quantity	1

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	



Current ECHA Candidate List: JAN 2025
(247)
Candidate List Declared Against: JAN 2025
(247)
Does not contain REACH SVHC

Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-111446-8
020 UNIV I/O 30DP NO EARS



TE Part # 1-111504-8
024 UNIV I/O 30DP NO EARS LTCH

Customers Also Bought



TE Part #3-647002-4
04P MTA100 PSTD CONN ASSY LF



TE Part #59824-1
TETRA-CRIMP PIDG PG FASTON 22-10 ASSY



TE Part #172157-1
2CIR MINI U-M-N-L CAP NATL




TE Part #1-794612-1
PIN CONT 20-24 15 GOLD L/P



TE Part #66102-9
III+ PIN, 24-20, 30AU/FL, STRIP




TE Part #102387-3
16 MODIV HSG COMP DR .100 POL




TE Part #1-104480-3
SHORT POINT CONT 30 DPLX
STMPD LF



TE Part #3-640443-5
05P MTA100 CONN ASSY GRN



TE Part #87667-5
MOD IV RECP LP



TE Part #794615-8
PANEL MT DBL ROW HSG 8 POS

Documents

Product Drawings

020 UNIV I/O STRAIN RELIEF

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_111547-4_N.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_111547-4_N.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_111547-4_N.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Ribbon Cable Interconnect Solutions

English

Product Specifications

Application Specification

English