

Features

- **Single Row Deep Groove Ball Bearing**
- **Pressed Steel Cage**
- **Both Sides Shielded**

RS PRO Ball Bearings

RS Stock No.: 0291649



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Single row deep groove ball bearings are the most widely used bearing type and are particularly versatile. They have low friction and are optimized for low noise and low vibration, which enables high rotational speeds. They can accommodate radial and axial loads in both directions, are easy to mount, and require less maintenance than many other bearing types.

A shielded Bearing is used in any environment where contamination is not a major issue. Usually specified for applications where the designer desires low starting and running torque as well as enclosing the bearing limiting the ingress of minor contaminants such as dust.

General Specifications

Ball Bearing Type	Single Row Deep Groove Ball Bearing
Sealing Arrangement	Both Sides Shielded
Number of Rows	1
Material	Steel
Ball Material	Steel
Cage Material	Steel
Race Material	Steel
Race Type	Plain
Bore Type	Parallel
Seals / Shields	Shielded
Clearance Code	CN
Bearing Series	2 Light

Mechanical Specifications

Inside Diameter (d)	20mm
Outside Diameter (D)	42mm
Race Width (B)	8mm
Static Load Rating	4.5kN
Dynamic Load Rating	7.95kN
Limiting Speed	21000 r/min
Mass	0.04 Kg

