

## Head for key selector switch, Harmony XB5, XB4, Ø22 mm 2 position stay put 5 multichips

Local distributor code: 409065714

ZB5AG2C

! Discontinued on: 9 Feb 2023

(!) Discontinued

EAN Code: 3389110851007

### Main

Range of product	Harmony XB5	
Product or component type	Head for key selector switch	
Device short name	ZB5	
Bezel material	Dark grey plastic	
Mounting diameter	22.5 mm	
Head type	Standard	
Sale per indivisible quantity	1	
Shape of signaling unit head	Round	
Type of operator	stay put	
Operator profile	Black key switch	
Operator position information	2 positions 90°	
Type of keylock	Special key	
Key withdrawal position	Left	

### Complementary

CAD overall width	29 mm
CAD overall height	29 mm
CAD overall depth	72 mm
Mechanical durability	1000000 cycles
Electrical composition code	C4 for <6 contacts using single and double blocks in front mounting C5 for <5 contacts using single blocks in front mounting C6 for <5 contacts using single and double blocks in front mounting C7 for <4 contacts using single blocks in front mounting C8 for <4 contacts using single and double blocks in front mounting C11 for <3 contacts using single blocks in front mounting C3 for <6 contacts using single blocks in front mounting SF1 for <3 contacts using single blocks in front mounting SR1 for <3 contacts using single blocks in rear mounting C15 for <1 contacts using single blocks in front mounting

### **Environment**

Protective treatment	тн
Ambient air temperature for storage	-4070 °C
Ambient air temperature for operation	-2570 °C
Overvoltage category	Class II conforming to IEC 60536

IP degree of protection	IP65 conforming to IEC 60529	
Resistance to high pressure washer	7000000 Pa at 55 °C, distance : 0.1 m	
IK degree of protection	IK06 conforming to IEC 50102	
Standards	GB/T 14048.1 GB/T 14048.5 IEC 60947-5-1 IEC 60947-1	
Product certifications	ccc	
Vibration resistance	5 gn (f= 2500 Hz) conforming to IEC 60068-2-6	
Shock resistance	30 gn (duration = 18 ms) for half sine wave acceleration conforming to IEC 60068-2-27 50 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-27	

# **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.4 cm
Package 1 Width	8.8 cm
Package 1 Length	3.4 cm
Package 1 Weight	51.0 g

### **Contractual warranty**

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

#### Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	1
Environmental Disclosure	Product Environmental Profile

### **Use Better**

Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	F28cb399-1b6a-409d-ac7b-4169e47b25c8
REACh Regulation	REACh Declaration
China RoHS Regulation	China RoHS declaration

### **Use Again**

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No