

SOL-SC-2ST-0-DC-4MPPT-1000EQSE - String combiner box (SCB)



1491583

<https://www.phoenixcontact.com/gb/products/1491583>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

String combiner box for photovoltaic systems up to 1000 V DC for connecting 4x 2 strings. Same number of input and output strings. With surge protection (type 1/2) and cable glands for the input and output side. Connection of the MPP trackers divided between two housings.



Product description

The Solarline string combiner boxes (SCBs) are used in both small rooftop systems and large ground-mounted systems. The main tasks of the SCBs are the surge protection of the photovoltaic system, collecting strings (if necessary), and looping through the protective equipotential bonding conductor for the local equipotential bonding.

Further functions are optional and depend on the equipment.

Examples of optional functions include protecting the strings with string fuses and disconnecting the strings via DC switch disconnectors or DC fire department switches.

You can determine the full scope of functions of the SCB from its item designation (see the application note for the type key of the SCB, which can be downloaded in the "Downloads" area).

Your advantages

- Fast installation and startup
- Standard-compliant switchgear and controlgear assembly, thanks to use of DIN EN 61439
- Application-oriented consultation
- Large portfolio of string combiner boxes in stock

Commercial data

Item number	1491583
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DTHTAA
Product key	DTHTAA
GTIN	4063151938284
Weight per piece (including packing)	5 kg
Weight per piece (excluding packing)	4 kg
Customs tariff number	85371098
Country of origin	DE

SOL-SC-2ST-0-DC-4MPPT-1000EQSE - String combiner box (SCB)



1491583

<https://www.phoenixcontact.com/gb/products/1491583>

Technical data

Notes

Note on connection (strings)

Notes on connection	Identical number of input and output strings
---------------------	--

Note on connection (MPP tracker)

Notes on connection	Connection of MPP trackers is divided between 2 housings
---------------------	--

Product properties

Product type	String combiner box (SCB)
Design	without special equipment

Insulation characteristics

Protection class	II
------------------	----

Electrical properties

General

MPP voltage U_n	max. 1000 V DC
Non-load voltage U_{OC}	max. 1100 V DC
Current per string I_{max}	max. 20 A
Total current MPP tracker	max. 40 A

Surge protection

EN type	T1
IEC test classification	T1
Protection level U_p	≤ 3.5 kV
Total discharge current I_{Total} (10/350) μs	5 kA
Total discharge current I_{Total} (8/20) μs	40 kA
Short-circuit current rating I_{SCPV}	40 A

Input data

Number of inputs: Strings	2 (Per MPP tracker)
Number of supported MPP trackers	4

Output data

DC

Number of outputs: MPP tracker	4
Number of outputs: $\pm$	2 (Per MPP tracker)

Connection data

DC input

SOL-SC-2ST-0-DC-4MPPT-1000EQSE - String combiner box (SCB)



1491583

<https://www.phoenixcontact.com/gb/products/1491583>

Type of cable entry	Cable gland
Connection method	Push-in connection
Cable cross-section range:	4 mm ² ... 6 mm ²
External cable diameter	3 mm ... 6.5 mm

Protective bonding and protective grounding conductor

Type of cable entry	Cable gland
Connection method	Push-in connection
Cable cross-section range:	2x 16 mm ²
External cable diameter	2x 6 mm ... 12 mm

DC output

Type of cable entry	Cable gland
Connection method	Push-in connection
Cable cross-section range:	4 mm ² ... 6 mm ²
External cable diameter	3 mm ... 6.5 mm

Dimensions

Housing

Width	508 mm
Height	180 mm
Depth	111 mm

Material specifications

Material Housing	Polycarbonate
Material Cover/door	Polycarbonate (transparent)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
Ambient temperature (operation)	-20 °C ... 50 °C

Standards and regulations

Standard designation	Low-voltage switchgear and controlgear assemblies - Part 2: Power switchgear and controlgear assemblies
Standards/specifications	EN 61439-2


SOL-SC-2ST-0-DC-4MPPT-1000EQSE - String combiner box (SCB)

1491583


<https://www.phoenixcontact.com/gb/products/1491583>

Drawings

Connection diagram




Schematic application drawing



Connection of the remote indication contact on the surge protection

Schematic diagram



SOL-SC-2ST-0-DC-4MPPT-1000EQSE - String combiner box (SCB)



1491583
<https://www.phoenixcontact.com/gb/products/1491583>

Classifications

ECLASS

ECLASS-13.0	27171490
-------------	----------

ETIM

ETIM 9.0	EC003857
----------	----------

SOL-SC-2ST-0-DC-4MPPT-1000EQSE - String combiner box (SCB)



1491583

<https://www.phoenixcontact.com/gb/products/1491583>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk