

Cotton cloth labels, manual marking

HELASIGN, Material 270 (Yellow), Booklet


For fast on-site identification of component parts, switching devices and other operating equipment.

Features and Benefits

- Yellow fabric adhesive labels
- Supplied in handy pocket-sized booklets
- Booklet cover protects labels when stored
- Easily remove or reposition labels as required
- No sticky residue on removal
- Labels available with or without black border
- Use T82 marker pen for market leading mark endurance



Always on hand: Labels in a convenient, pocket sized and lightweight booklet.



MATERIAL	Type 270, Cotton cloth, yellow (YE)
Operating Temperature	-29 °C to +80 °C
Curing Temperature	from +10 °C
Adhesive	Synthetic rubber
Thickness of Foil (µm)	150 µm
Chem. Material Properties	Good resistance against water, oils and most solvents.



TYPE	Description	Width (W)	Height (H)	Labels per Sheet	Pack Cont.	Colour	Article-No.
TAG122FB-270-YE	With border	15.0	9.0	70	700 pcs.	Yellow (YE)	598-92227
TAG124FB-270-YE		19.0	11.0	44	440 pcs.	Yellow (YE)	598-92427
TAG121FB-270-YE		20.0	8.0	60	600 pcs.	Yellow (YE)	598-92127
TAG125FB-270-YE		38.0	11.0	22	220 pcs.	Yellow (YE)	598-92527
TAG122B-270-YE	Without border	15.0	9.0	70	700 pcs.	Yellow (YE)	598-12227
TAG120B-270-YE		15.0	6.0	105	1,050 pcs.	Yellow (YE)	598-12027
TAG124B-270-YE		19.0	11.0	44	440 pcs.	Yellow (YE)	598-12427
TAG121B-270-YE		20.0	8.0	60	600 pcs.	Yellow (YE)	598-12127

All dimensions in mm. Subject to technical changes.

Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available.

TYPE	Description	Colour	Pack Cont.	Article-No.
T82S-BK	Indelible Marker Pen	Black (BK)	2 pcs.	500-50820
T82R-RD	Indelible Marker Pen	Red (RD)	2 pcs.	500-50822

Subject to technical changes.

Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available.