



PRODUCT-DETAILS

CK1-11

CK1-11 Short-Circuit Signaling Contact 1 NO + 1 NC



概要信息	
产品型号	CK1-11
产品ID	1SAM301901R1001
欧洲商品编号(EAN)	4013614403927
目录说明	CK1-11 Short-Circuit Signaling Contact 1 NO + 1 NC
详细描述	Signaling contacts CK1 with screw terminals signal the tripping of the manual motor starter in case it was caused by a short-circuit. For CK1 the indication on the device itself is done with a protruding orange button. The contact positions of CK1 need to be manually reset after a tripping event by pushing the orange button. They are attached on the right side of the manual motor starter MS116, MS132 or MS165. Signaling contacts CK1 are available as normally open or normally closed contacts.

订货信息	
最小起订量	2 piece
海关关税号	85365080

Popular Downloads

数据手册，技术资料	1SBC100214C0202
说明书和手册	2CDC131027M6802
	2CDC131081M6801
说明书和手册（第3部分）	1SBC100214C0202
CAD Dimensional Drawing	2CDC001079B0201

尺寸

产品净宽	9 mm
产品净高	90 mm
产品净深	78 mm
产品净重	0.035 kg

技术参数

端子类型	Screw Terminals
额定工作电压	690 V AC 600 V DC Main Circuit 690 V
额定工作电流 AC-15 (I _e)	(24 V) 6 A (240 V) 4 A (690 V) 1 A (380 / 400 V) 3 A
额定工作电流 DC-13 (I _e)	(24 V) 2 A (125 V) 0.55 A (250 V) 0.27 A (440 V) 0.15 A (600 V) 0.15 A
额定冲击耐受电压 (U _{imp})	Auxiliary Circuit 6 kV
额定绝缘电压 (U _i)	690 V
防护等级	IP20
电气寿命	10000 cycle
机械寿命	10000 cycle
辅助电路连接容量	Flexible with Ferrule 1/2x 0.75 ... 1.5 mm ² Flexible with Insulated Ferrule 1/2x 0.75 ... 1.5 mm ² Flexible 1/2x 0.75 ... 1.5 mm ² Rigid 1/2x 1 ... 1.5 mm ²
拧紧力矩	Auxiliary Circuit 0.8 ... 1.2 N·m
剥线长度	Auxiliary Circuit 8 mm
推荐的螺丝刀	M3 Pozidriv 2
辅助触点NO数量	1
辅助触点NC数量	1
产品	Short Circuit Signaling Contact
适用于	MS132 MS165
适用产品系列	Manual Motor Starter
配件组别	Electrical
配件类型	Short Circuit Signaling Contact

UL/CSA适用的技术参数

最高工作电压UL/CSA	Main Circuit 600 V AC
辅助电路连接容量	Flexible 1/2x 16-14 AWG
UL/CSA	Stranded 1/2x 16-14 AWG

拧紧力矩UL/CSA	Auxiliary Circuit 7 in-lb
接触等级UL/CSA	B600
	Q600

环境条件

周围环境温度	Operation -25 ... +60 °C Storage -50 ... +80 °C
抗机械冲击符合IEC 60068-2-27标准	11 ms Pulse 25g
耐振动符合IEC 60068-2-6标准	5g 3 ... 150 Hz

Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	1SAA963005-4502
RoHS信息	1SAA963006-4502
RoHS状态	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA	2CMT2023-006539
WEEE B2C / B2B	Business To Business
WEEE 类别	5. Small Equipment (No External Dimension More Than 50 cm)

认证及声明（文件编码）

A2L Certificate – IEC	1SAA963000-4601
ABS认证	1SAA963001-0101
BV认证	1SAA963002-0201
CB认证	1SAA963004-2002
CQC认证	CQC2017010304032778
cUL 认证	cUL_E137861
Declaration of Conformity - CCC	2020980304001252
符合性声明 - CE	1SAD101100-3410
Declaration of Conformity - UKCA	1SAD201100-3410
DNV GL Certificate	1SAA963001-0304
LR认证	1SAA963001-0502 1SAA918001-0501
RINA认证	1SAA963002-0802
UL认证	UL_E137861

包装信息

1级包装宽度	25 mm
1级包装长度	80 mm
1级包装高度	93 mm
1级包装 总重	0.08 kg
1级包装 EAN	4013614481529
1级包装单元	box 2 piece
2级包装宽度	280 mm

2级包装长度	395 mm
2级包装高度	210 mm
2级包装 EAN	4013614526015
2级包装单元	160 piece

分类

对象分类代码	Q
ETIM 4	EC002498 - Accessories for low-voltage switch technology
ETIM 5	EC000041 - Auxiliary contact block
ETIM 6	EC000041 - Auxiliary contact block
ETIM 7	EC000041 - Auxiliary contact block
ETIM 8	EC000041 - Auxiliary contact block
e级	V11.0 : 27371302
UNSPSC	39121522
IDEA 粒度分类代码 (IGCC)	4743 >> Auxiliary contact block
E-Number (Finland)	3706160
E-Number (Norway)	4364490
E-Number (Sweden)	3110145

分类

低压产品及系统 → 控制产品 → 电动机起动器 → 电动机起动器
低压产品及系统 → 断路器类产品 → 电动机起动器

