


FEATURES

- **Polyacrylic material:** Offers excellent durability and resistance to wear, ensuring long-lasting performance.
- **Maximum operating pressure of 2000 kPa:** Suitable for high-pressure applications, providing reliable sealing.
- **Maximum operating temperature of 200 °C:** Capable of withstanding high temperatures, ideal for thermal-intensive environments.
- **Rotary speed of 10 m/s:** Supports high-speed operations, enhancing versatility.
- **Section size of 6.5 mm:** Provides a compact and efficient sealing solution.

RS PRO 8m Polyacrylic Gland & Valve Packing

RS Stock No: 606-581



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO gland and valve packing is designed for sealing applications in industrial environments. Made from durable polyacrylic material, it provides reliable sealing under high pressure and temperature conditions, making it ideal for use in pumps and valves. The packing is engineered to withstand a maximum operating pressure of 2000 kPa and a temperature of up to 200 °C, ensuring optimal performance in demanding settings.

General Specifications

Maximum Operating Pressure	2000 kPa
Product Type	Gland & Valve Packing
Rotary Speed	10 m/s
Section	6.5 mm
Sub Type	Gland Packing

Mechanical Specifications

Length	8 m
Material	Polyacrylic

Operation Environment Specifications

Maximum Operating Temperature	200 °C
-------------------------------	--------

Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, RoHS
---------------------	----------------------------