



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Receptacle**
Connector & Housing Type: **Receptacle**
Number of Positions: **1**
Terminal Orientation: **Straight**
UL Flammability Rating: **UL 94V-0**

Features

Product Type Features

Connector & Contact Terminates To	Wire & Cable
Sealable	No
Connector System	Wire-to-Board, Wire-to-Wire
Connector & Housing Type	Receptacle

Configuration Features

Number of Positions	1
---------------------	---

Body Features

Primary Product Color	Blue
-----------------------	------

Contact Features

Terminal Type	Receptacle
Terminal Orientation	Straight
Contact Mating Retention	With

Mechanical Attachment

--



Mating Alignment Type	Polarization
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Nylon
------------------	-------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	1000
--------------------	------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Melamine (3% in 23457018694) Article Safe Usage Statements: Wash thoroughly after handling. Do not handle until all safety precautions have been read and understood. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability




Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides




on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 368612-2 POSITIVE LOCK 250 TERMINAL-FLAG	 TE Part # 170331-1 PL MKII 187 REC 20-16AWG PTBR LP	 TE Part # 170330-1 PL MKII 187 REC 24-20AWG PTBR LP	 TE Part # 3-173974-7 PL MKII 187 REC HSG 1P NYLON GWT RED
 TE Part # 170332-1 PL 187 RECEPTACLE 18-14 AWG PTPBR	 TE Part # 170326-5 187 PL MKII REC. 18-14AWG PTPB	 TE Part # 170330-2 PL 187 RECEPTACLE 24-20 AWG NPPHBZ	 TE Part # 3-173974-6 PL MKII 187 REC HSG 1P NYLON GWT BLU
 TE Part # 170326-1 187 PL MKII REC. 18-14AWG PTBR	 TE Part # 170324-2 PL 187 RECEPTACLE 24-20 AWG 0.3 NPCU	 TE Part # 170324-1 187 PL MKII REC. 24-20AWG PTBR	 TE Part # 170325-1 187 PL MKII REC. 20-16AWG PTBR
 TE Part # 170325-5 187 PL MKII REC. 20-16AWG PTBR			

Also in the Series | Positive Lock 187




Crimp Terminal Housings(76)



Insertion & Extraction Tools(2)




Insulation Boots & Sleeves(7)



Quick Disconnects(57)

Also in the Series


Mark II



Automotive Connector Locks & Position Assurance(1)




Automotive Housings(6)



Automotive Terminals(3)



Connector Seals & Cavity Plugs(1)



Crimp Terminal Housings(76)



Insertion & Extraction Tools(2)



Quick Disconnects(57)

Customers Also Bought



TE Part #1969820-1
250 HIGH TEMP POS LOCK HSG LCP



TE Part #7-534206-5
50 MODII VRT DR CE 100/115



TE Part #2337224-1
TACT ULTRA TB 2.6X1.6X0.55 160GF




TE Part #1982299-1
ELCON MINI 2P CABLE CONN,WITH CODING(R)




TE Part #170324-1
187 PL MKII REC. 24-20AWG PTBR



TE Part #2238106-1
250 POS LOCK REC FLAG 12-10



TE Part #173974-7
PL 187 (4.8 MM) HOUSING RECEPTACLE



TE Part #2238104-1
250 PL MKII REC. 16-14AWG NPST



Documents

Product Drawings

PL MKII 187 REC HSG 1P NYLON BLUE

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_173974-6_P.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_173974-6_P.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_173974-6_P.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Positive Lock Receptacles

English

Product Specifications

Product Specification

English

JAPANESE

English

Agency Approvals

UL Report

English