



PRODUCT-DETAILS

OT125GFCC6T

OT125GFCC6T Safety switch



General Information

Extended Product Type	OT125GFCC6T
Product ID	1SCA148668R1001
EAN	6417019780870
Catalog Description	OT125GFCC6T Safety switch
Long Description	Safety switch, 6-p. 415V AC23 125A, 55kW. Mounted auxiliary contact: 2NO2NC. Plastic enclosure. IP65. Black Pistol handle. Interlocked cover. Defeatable interlocking. The enclosure in the OT series is using a rigid glass reinforced polycarbonate enclosure. The enclosure is UV protected, protected against low-pressure water jets (IP65), and hence built for outdoor and indoor use. The cable entries knock out types for II-flanges. Cables can be inserted from top and bottom. The handle is padlockable and made for three padlocks. The cover is interlocked. The interlocking can be defeated. PE terminals included.

Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	1SCC340076D0201
RoHS Declaration	1SCC340075D0201

RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA	1SCC340095D0201

Popular Downloads

Data Sheet, Technical Information	1SCC340015C0201
Instructions and Manuals	1SCC340015M0004
Mechanical Drawings	OTPK563818PIL.stp

Environmental

Degree of Protection	acc. to IEC 60529 IP65
Pollution Degree	3

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85363030
Country or Territory of Origin	Finland

Dimensions

Product Net Width	380 mm
Product Net Height	560 mm
Product Net Depth / Length	180 mm
Product Net Weight	8 kg

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	415 mm
Package Level 1 Depth / Length	710 mm
Package Level 1 Height	325 mm
Package Level 1 Gross Weight	9.9 kg
Package Level 1 EAN	6417019780870

Technical

Cable Cross-Section	10 ... 70 mm ²
Cable Entry Position	Top/Bottom
Cable Outlets Per Side	II-flange / II-flange
Color	RAL7035
Connecting Capacity Main Circuit	Screw Clamp 10 ... 70 mm ² Screw Clamp / PE Terminal 2pc, 10 ... 70 mm ²
Conventional Thermal Current (I _{the})	Fully Enclosed 125 A

Degree of Protection	acc. to IEC 60529 IP65
Enclosure Material	Plastic
Enclosure Type	Fibox
Handle Color	Black
Handle Type	Pistol handle
Impact Resistance Rating	Housing IK08
Maximum Mounted Auxiliary Contacts	2 NO, 2 NC
Mounted Auxiliary Contacts	2 NO, 2 NC
Neutral Type	No Neutral Terminal
Number of Auxiliary Contacts NC	2
Number of Auxiliary Contacts NO	2
Number of Poles	6P
Pollution Degree	3
Position of Line Terminals	Top In - Bottom Out
Rated Conditional Short-Circuit Current (I_{nc})	24 kA
Rated Impulse Withstand Voltage (U_{imp})	12 kV
Rated Insulation Voltage (U_i)	750 V
Rated Operational Current AC-22A (I_e)	(380 ... 415 V) 125 A (500 V) 125 A (690 V) 125 A
Rated Operational Current AC-23A (I_e)	(380 ... 415 V) 125 A (500 V) 125 A (690 V) 125 A
Rated Operational Power AC-23A (P_e)	(380 ... 415 V) 55 kW (500 V) 75 kW (690 V) 110 kW
Rated Operational Voltage	Main Circuit 1000 V
Rated Short-Circuit Making Capacity (I_{cm})	(690 V AC) 12 kA
Rated Short-time Withstand Current Low Voltage (I_{cw})	for 1 s 4 kA
Recommended Screw Driver	Main Circuit Hexagon 4
Standards	IEC 60947-1, -3
Terminal Type	Screw Terminals
Tightening Torque	Main Circuit 6 N·m
Wire Stripping Length	20 mm

Technical UL/CSA

Wire Stripping Length	20 mm
Recommended Screw Driver	Main Circuit Hexagon 4
Tightening Torque	Main Circuit 6 N·m

Certificates and Declarations

Declaration of
Conformity - CE

1SCC340002D2703

External Classifications and Standards

Object Classification Code	Q
ETIM 9	EC000216 - Switch disconnecter (low voltage)
ETIM 10	EC000216 - Switch disconnecter (AC)
UNSPSC	39122205
IDEA Granular Category Code (IGCC)	5166 >> Safety switch
eClass	V11.1 : 27371403
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
E-Number (Sweden)	3134577

Categories

Low Voltage Products and Systems → Enclosed Switches → Enclosed Safety Switches → Enclosed Safety Switches

