


# PARALLEL BENCH VICE

EGA Master offers a wide variety of pipe tools, Mastergrip wrenches, Stillson, Heavy Duty, Swedish pipe wrenches, Threaders, Tube cutters, Bench vice, etc.



**Forged  
type**



**1.**

- Knurled jaws for a better grip (interchangeable).
- Heat treated for increased strength.
- Perfect alignment relative to longitudinal axis, transversal and in height.

**2.** Pipe jaws.

**3.** Force up to 50.000N "Forged type".






**4.** Practice and wide area sweetspot.

**5.** Adaptable swivel base (optional).

**6.** Different lubrication points for perfect maintenance.


**7.** Swivel lever that allows a smooth shift.

■ **FIXED**





COD.				N		
57619	4	100	1/4-1.1/4	15000	7,0	1
57620	5	150	1/4-1.1/2	25000	11	
57621	6	200		35000	17	
57622	7	225	1/2-3	50000	27	

**FEATURES**

Made of accurate ductile cast steel - "Forged type"



■ **SWIVEL**


COD.			N		
57624	4	100	15000	8,0	1
57625	5	150	25000	12	
57626	6	200	35000	18	
57627	7	225	50000	29	


**FEATURES**

Made of accurate ductile cast steel - "Forged type"



■ **SPARE PARTS**

COD.	(inch)	
86580	4	0,8
86581	5	1,0
86582	6	1,3
86583	7	1,4

COD.	(inch)	
86584	4	0,7
86585	5	0,9
86586	6	1,1
86587	7	1,3



**CARACTERÍSTICAS TÉCNICAS**

MATERIAL	Body: Made of accurate ductile cast steel - "Forged type" Jaws: Special steel
FINISH	Body: Blue Pantone 534C Jaws: Polished
HARDNESS	Interchangeable jaws: 40 HRc Pipe jaws for fixing: 45-50 HRc.