

**PART NUMBER:**

RS Part No. 234 102.

**DESCRIPTION:**

"Eurotuf" High Impact Resistant Cable, 2-core, 1.5mm<sup>2</sup>.

**CONDUCTORS:**

1.5mm<sup>2</sup> plain annealed copper wire meeting the requirements of BS 6360, class 1.  
Maximum resistance at 20°C = 12.1Ω/km.

**INSULATION:**

Type TI 1 PVC compound meeting the requirements of BS EN 50363.  
Minimum average radial thickness = 0.6mm.

**LAY UP:**

One Blue and one Brown core.

**OUTER SHEATH 1:**

PVC compound.  
Nominal radial thickness = 0.85mm.  
Minimum diameter = 6.75mm.  
Maximum diameter = 7.15mm.

**OUTER SHEATH 2:**

Hard grade PVC compound.  
Nominal radial thickness = 0.85mm.  
Minimum diameter = 8.45mm.  
Maximum diameter = 8.85mm.

**CABLE WEIGHT:**

Approximately 107kg/km.