

Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

Supplier's name or trade mark: di-soric

Supplier's address: Environmental, Gielster Stück 2, 58513 Lüdenscheid, DE

Model identifier: MB-N-251-K-B3 / 210196

Type of light source:

Lighting technology used:	LED	Non-directional or directional:	DLS
Light source cap-type (or other electric interface)	offene Kabelenden		
Mains or non-mains:	NMLS	Connected light source (CLS):	No
Colour-tuneable light source:	No	Envelope:	-
High luminance light source:	No		
Anti-glare shield:	No	Dimmable:	No


Product parameters

Parameter	Value	Parameter	Value
General product parameters:			
Energy consumption in on-mode (kWh/1000 h), rounded up to the nearest integer	11	Energy efficiency class	E
Useful luminous flux (ϕ_{use}), indicating if it refers to the flux in a sphere (360°), in a wide cone (120°) or in a narrow cone (90°)	1 100 in Wide cone (120°)	Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set	5 000
On-mode power (P_{on}), expressed in W	10,8	Standby power (P_{sb}), expressed in W and rounded to the second decimal	0,00
Networked standby power (P_{net}) for CLS, expressed in W and rounded to the second decimal	-	Colour rendering index, rounded to the nearest integer, or the range of CRI-values that can be set	85
Outer dimensions without separate control gear, lighting control	Height	Spectral power distribution in the range 250 nm to 800 nm, at full-load	See image in last page
	Width		
	Depth		


parts and non-lighting control parts, if any (millimetre)				
Claim of equivalent power ^(a)	-	If yes, equivalent power (W)	-	
		Chromaticity coordinates (x and y)	0,344 0,355	
Parameters for directional light sources:				
Peak luminous intensity (cd)	386	Beam angle in degrees, or the range of beam angles that can be set	120	
Parameters for LED and OLED light sources:				
R9 colour rendering index value	9	Survival factor	1,00	
the lumen maintenance factor	0,98			

(a) : not applicable;

(b) : not applicable;



Model placed on the Union market from 03/03/2017



EPREL registration number: 1853632

<https://eprel.ec.europa.eu/qr/1853632>

Supplier: di-soric GmbH & Co. KG (Manufacturer)

Website: <https://www.di-soric.com>

Customer care service:

Name: Environmental

Website: www.di-soric.com

Email: info@di-soric.com

Phone: +49 (0) 2351 / 9844-402

Address:

Gielster Stück 2
58513 Lüdenscheid
Germany