

LJ8K09Q714

Enclosed reversing starter, TeSys LJ, 6-10A, 24V
AC coil, including 2 LC1K, GV2ME, integral
transformer, pushbutton, 2-pos switch, GVAX

Main

Range	TeSys
Product name	TeSys LJ
Device short name	LJ8K
Product or component type	Enclosed DOL reversing starter
Device application	Safety
Utilisation category	AC-3
Device composition	Reversing contactor Control transformer Circuit-breaker
Motor power kW	4 kW at 380/400 V AC 50 Hz
Thermal protection adjustment range	6...10 A
[Uc] control circuit voltage	24 V AC 50/60 Hz
Control type	Push-button stop black O Selector switch 2 positions start black I-II Mushroom head push-button emergency stop red

Complementary

Cable entry number	4 2 Pg 13 + 2 Pg 16 top 4 2 Pg 13 + 2 Pg 16 bottom
Width	175 mm
Height	165 mm
Depth	146 mm
Net weight	2.65 kg

Environment

Standards	IEC 60947-4-1 IEC 60204-1
Material	Polycarbonate
IP degree of protection	IP55 conforming to IEC 60529 (for enclosure)
IK degree of protection	IK07 conforming to IEC 60529
Environmental characteristic	Standard environment

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins