



GAXSW

housing: heat-treating steel to 42CrMo4, forged, zinc plated
insert: free-cutting steel to 11SMnPb30C, zinc plated
ball: bearing steel to 100Cr6, hardened, ground, polished



part	D (H7)	B	M	A	F	L	G	GL	static load C0 (kN)	dynamic load C (kN)	α
GAXSW30x1,5	30	37	25	70	110	145	M30x1,5	71	184	168	17