

Data sheet

Commercial Art.No.: 96.031.5054.3

device connector RST25I3S B1 M01V BG03

RST® CLASSIC device connector, standard, straight, M25, number of poles 3, model female, connection type screw connection, rated voltage 250 V / 400 V, rated current 25 A, color of coding/ contact carrier concrete grey



Commercial Art.No.	96.031.5054.3
EAN	4015573864085
Order Unit	1

certificates / approvals



Technical data

general

rated current	25 A
rated voltage	250 V / 400 V
pollution degree	3
rated impulse voltage	4 kV
continuity resistor	0.55 mOhm
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	concrete grey
marking of poles	L, N, PE
color of separate adapter (if present)	black

connection data

connection cross section solid mm² max.	6 mm²
connection cross section solid mm² min.	0.75 mm²
connection cross section fine stranded mm² max.	6 mm²
connection cross section fine stranded mm² min.	0.75 mm²
terminations per pole	1
wire strip length	8 mm

technical data UL

connection cross section solid AWG min.	16 AWG
connection cross section solid AWG max.	10 AWG
connection cross section stranded AWG min.	16 AWG

model

model	female
connection type	screw connection
connecting thread metric	M25
angle of plug	straight
degree of protection (IP)	IP66/68 (3m;2h) /IP69
thickness of housings (electrical device)	0.5 mm
thickness of housings (electrical device)	8 mm

material

housing material	polyamide
halogen free	yes
contact material	CuZn
fire load	0.131 kWh/St
insulation components continuous temperature	100 °C
surface finish	silver-plated

dimensions

length	50.5 mm
width	35 mm
height	35 mm

note

note	RST® terminals with screw clamping allow the connection of conductors without special preparation (without ferrules) according to EN 60999-1.; positioning realised with flattened thread
------	---

classification

ECLASS 11	
ECLASS 8.1	27440602
ETIM 9.0	EC002566
ETIM 8.0	EC002566
ETIM 7.0	EC002566
ETIM 6.0	EC002566
ETIM 5.0	EC002566
ETIM 4.0	EC002566

product compliance

ROHS conformity status	compliant/exempted
ROHS exceptions	III-6(c)
REACH-SVHC conformity status	Duty-To-Declare
REACH-SVHC substances	Lead
REACH-SVHC CAS numbers	7439-92-1

Fits with

Commercial Art.No.:	Article-type description:	Description:
---------------------	---------------------------	--------------

96.032.4154.3	connector RST25I3S S1 ZR2 V BG03	RST® CLASSIC connector, straight, number of poles 3, male, connection type screw connection, rated voltage 250 V, rated current 25 A, cable diameter 10 - 14 mm, color of coding/ contact carrier concrete grey
96.034.4154.3	connector RST25I3S S1 YR2SV BG03	RST® CLASSIC connector, angled 90°, number of poles 3, male, connection type screw connection, rated voltage 250 V, rated current 25 A, cable diameter 10 - 14 mm, color of coding/ contact carrier concrete grey
96.032.4554.3	connector RST25I3S S1 ZR3SV BG03	RST® CLASSIC connector, straight, number of poles 3, male, connection type screw connection, rated voltage 250 V, rated current 25 A, cable diameter 13 - 18 mm, color of coding/ contact carrier concrete grey
96.032.4054.3	connector RST25I3S S1 ZR1SV BG03	RST® CLASSIC connector, straight, number of poles 3, male, connection type screw connection, rated voltage 250 V, rated current 25 A, cable diameter 6 - 10 mm, color of coding/ contact carrier concrete grey
96.034.4054.3	connector RST25I3S S1 YR1SV BG03	RST® CLASSIC connector, angled 90°, number of poles 3, male, connection type screw connection, rated voltage 250 V, rated current 25 A, cable diameter 6 - 10 mm, color of coding/ contact carrier concrete grey
96.032.4454.3	connector RST25I3S S1AZRW V BG03	RST® CLASSIC connector, straight, for illumination cable, number of poles 3, male, connection type screw connection, rated voltage 250 V, rated current 25 A, cable diameter 5.3 - 13.3 mm, illumination cable (13.3x5.3), color of coding/ contact carrier concrete grey

1	2	3	4	5	6																																																																																									
A	These dimensions will be especially checked at delivery Only inspection dimensions With /E marked dimensions are only valid for internal use		Auslieferungszustand delivery status		Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.																																																																																									
B																																																																																														
C																																																																																														
D																																																																																														
E																																																																																														
F																																																																																														
Offnungsmassbild siehe 96.031.1053.1 14K opening dimension see 96.031.1053.1 14K			Verpackungseinheit: je 100 Stück packaging unit: per 100 <table><tr><td>96.031.5054.3</td><td>RST2513S B1 M01 BG03</td><td>betongrau /grey</td></tr><tr><td>Bestellnummer /Order number</td><td>Typ /Type</td><td>Farbe /color</td></tr><tr><td colspan="2">Weitere Daten siehe KATALOG oder eKatalog. Additional data see CATALOG or eCatalog.</td><td>www.wieland-electric.com eshop.wieland-electric.com</td></tr></table> Tolerierung Size ISO 14405(®)/Tolerance system Size ISO 14405(®). (This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances). nein/no ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten. Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared! <table><tr><td colspan="2">Freitoleranz nach General tolerance</td><td colspan="2">CAD - Zeichnung, keine manuellen Änderungen CAD - drawing, no manual modifications allowed</td><td colspan="2">1.Verwendung: - First Use:</td><td colspan="2">Blatt: 1 von 1 Sheet: 1 of 1</td></tr><tr><td colspan="2">/</td><td colspan="2">Werkstoff/Material</td><td colspan="2">2015 Tag/Date Name</td><td colspan="2">Zeichnung Nr./Drawing No.</td></tr><tr><td colspan="2">/</td><td colspan="2">Maßstab/Scale</td><td colspan="2">gezeichnet drawn 06.07. HoffmannT</td><td colspan="2">Index</td></tr><tr><td colspan="2">/</td><td colspan="2">1:1</td><td colspan="2">geprüft checked - -</td><td colspan="2">96.031.5054.3 13K</td></tr><tr><td colspan="2">/</td><td colspan="2">Vol. mm³ Ofl./Surf. mm²</td><td colspan="2">Normgepr. Stand. check - -</td><td colspan="2">Maße in mm/Dimensions are in mm</td></tr><tr><td colspan="2">/</td><td colspan="2">Vol. mm³ Ofl./Surf. mm²</td><td colspan="2">Ersatz für/Replacement for: -</td><td colspan="2"></td></tr><tr><td colspan="2">/</td><td colspan="2">Type</td><td colspan="2">Benennung/Title</td><td colspan="2"></td></tr><tr><td colspan="2">/</td><td colspan="2">www.wieland-electric.com</td><td colspan="2">BUCHSENTEIL female connector</td><td colspan="2"></td></tr><tr><td colspan="2">Index Datum / Blatt Date / Sheet</td><td colspan="2"></td><td colspan="2"></td><td colspan="2"></td></tr><tr><td colspan="2">Änderung/Revision</td><td colspan="2"></td><td colspan="2"></td><td colspan="2"></td></tr></table>			96.031.5054.3	RST2513S B1 M01 BG03	betongrau /grey	Bestellnummer /Order number	Typ /Type	Farbe /color	Weitere Daten siehe KATALOG oder eKatalog. Additional data see CATALOG or eCatalog.		www.wieland-electric.com eshop.wieland-electric.com	Freitoleranz nach General tolerance		CAD - Zeichnung, keine manuellen Änderungen CAD - drawing, no manual modifications allowed		1.Verwendung: - First Use:		Blatt: 1 von 1 Sheet: 1 of 1		/		Werkstoff/Material		2015 Tag/Date Name		Zeichnung Nr./Drawing No.		/		Maßstab/Scale		gezeichnet drawn 06.07. HoffmannT		Index		/		1:1		geprüft checked - -		96.031.5054.3 13K		/		Vol. mm³ Ofl./Surf. mm²		Normgepr. Stand. check - -		Maße in mm/Dimensions are in mm		/		Vol. mm³ Ofl./Surf. mm²		Ersatz für/Replacement for: -				/		Type		Benennung/Title				/		www.wieland-electric.com		BUCHSENTEIL female connector				Index Datum / Blatt Date / Sheet								Änderung/Revision							
96.031.5054.3	RST2513S B1 M01 BG03	betongrau /grey																																																																																												
Bestellnummer /Order number	Typ /Type	Farbe /color																																																																																												
Weitere Daten siehe KATALOG oder eKatalog. Additional data see CATALOG or eCatalog.		www.wieland-electric.com eshop.wieland-electric.com																																																																																												
Freitoleranz nach General tolerance		CAD - Zeichnung, keine manuellen Änderungen CAD - drawing, no manual modifications allowed		1.Verwendung: - First Use:		Blatt: 1 von 1 Sheet: 1 of 1																																																																																								
/		Werkstoff/Material		2015 Tag/Date Name		Zeichnung Nr./Drawing No.																																																																																								
/		Maßstab/Scale		gezeichnet drawn 06.07. HoffmannT		Index																																																																																								
/		1:1		geprüft checked - -		96.031.5054.3 13K																																																																																								
/		Vol. mm³ Ofl./Surf. mm²		Normgepr. Stand. check - -		Maße in mm/Dimensions are in mm																																																																																								
/		Vol. mm³ Ofl./Surf. mm²		Ersatz für/Replacement for: -																																																																																										
/		Type		Benennung/Title																																																																																										
/		www.wieland-electric.com		BUCHSENTEIL female connector																																																																																										
Index Datum / Blatt Date / Sheet																																																																																														
Änderung/Revision																																																																																														
960315054313K_1 CADW3034 HoffmannT 2015-07-15T12:54:17 1.000																																																																																														
3 4 5 6 QU-MEE-01/14 -																																																																																														