

FBS 1,5/S-PV - Potential bridge



3216263

<https://www.phoenixcontact.com/gb/products/3216263>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Vertical potential bridge, to connect the upper and lower level

Commercial data

| | |
|--------------------------------------|---------------------|
| Item number | 3216263 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BE2Z2X |
| Product key | BE2Z2X |
| Catalog page | Page 404 (C-1-2019) |
| GTIN | 4046356572064 |
| Weight per piece (including packing) | 0.64 g |
| Weight per piece (excluding packing) | 0.614 g |
| Customs tariff number | 85366990 |
| Country of origin | PL |

FBS 1,5/S-PV - Potential bridge

3216263

<https://www.phoenixcontact.com/gb/products/3216263>



Technical data

Product properties

| | |
|---------------------|-----------------|
| Product type | Vertical bridge |
| Number of positions | 1 |

Electrical properties

| | |
|----------------------|---|
| Maximum load current | 16 A (The current values for the jumpers can deviate when used in different modular terminal blocks. The precise values can be found in the accessories data for the respective modular terminal blocks.) |
|----------------------|---|

Connection data

| | |
|----------------------|---|
| Maximum load current | 16 A (The current values for the jumpers can deviate when used in different modular terminal blocks. The precise values can be found in the accessories data for the respective modular terminal blocks.) |
|----------------------|---|

Dimensions

| | |
|--------|---------|
| Width | 3.5 mm |
| Height | 3 mm |
| Depth | 33.7 mm |
| Length | 3 mm |

Material specifications

| | |
|---------------------|------------------|
| Color | black (RAL 9005) |
| Material | Copper |
| Insulating material | PA |

Environmental and real-life conditions

Ambient conditions

| | |
|--|--|
| Ambient temperature (operation) | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C |
| Permissible humidity (operation) | 20 % ... 90 % |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

Mounting

| | |
|---------------|------------------|
| Mounting type | Plug-in mounting |
|---------------|------------------|

FBS 1,5/S-PV - Potential bridge

3216263

<https://www.phoenixcontact.com/gb/products/3216263>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27250303 |
|-------------|----------|

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC000489 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

FBS 1,5/S-PV - Potential bridge

3216263

<https://www.phoenixcontact.com/gb/products/3216263>



Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk