

## AMPLIMITE

TE Internal #: 5786144-1

TE Internal Description: 15 RCPT ACT PIN/MS SCRLK

[View on TE.com >](#)

Connectors &gt; D-Shaped Connectors

Number of Positions: **15**Connector & Housing Type: **Receptacle**Connector System: **Board-to-Board**Connector Mounting Type: **Board Mount**Connector Shell Size: **2****Features****Product Type Features**

Shell Material Configuration	Front Metal Shell
Connector & Housing Type	Receptacle
Connector System	Board-to-Board
Connector Shell Size	2
Connector & Contact Terminates To	Printed Circuit Board

**Configuration Features**

Number of Positions	15
Number of Rows	2
PCB Mount Orientation	Vertical

**Body Features**

Shell Plating Material	Tin over Copper
Mating Feature Material	Brass
Primary Product Color	Black
Connector Profile	Standard

**Contact Features**

	30 µin
Contact Underplating Material	Nickel, Palladium Nickel
Contact Mating Area Plating Material	Gold (Au)
Contact Base Material	Copper Alloy

PCB Contact Termination Area Plating Material	Tin
---	-----

Contact Options	Installed
-----------------	-----------

### Termination Features

Rectangular Termination Post & Tail Width	.86 mm[.034 in]
---	-----------------

Rectangular Termination Post & Tail Thickness	.63 mm[.025 in]
---	-----------------

Termination Method to PCB	Through Hole - Press-Fit
---------------------------	--------------------------

Termination Post & Tail Length	5.8 mm[.228 in]
--------------------------------	-----------------

### Mechanical Attachment

Mounting Hole Diameter	3.05 mm[.12 in]
------------------------	-----------------

Connector Mounting Type	Board Mount
-------------------------	-------------

PCB Mount Retention	With
---------------------	------

PCB Mount Retention Type	Action/Compliant Tail, Mounting Hole
--------------------------	--------------------------------------

Mating Retention	With
------------------	------

Mating Retention Type	Female Screwlocks, Fixed
-----------------------	--------------------------

### Housing Features

Housing Material	Nylon GF, Polyester GF
------------------	------------------------

Shell Material	Carbon Steel
----------------	--------------

Centerline (Pitch)	2.74 mm[.108 in]
--------------------	------------------

### Dimensions

PCB Thickness (Recommended)	1.57 mm, 2.36 mm[.062 in][.093 in]
-----------------------------	------------------------------------

Row-to-Row Spacing	2.84 mm[.112 in]
--------------------	------------------

### Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

### Operation/Application

Circuit Application	Signal
---------------------	--------

### Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

### Packaging Features

Packaging Quantity	104
--------------------	-----

Packaging Method	Tray
------------------	------

### Product Compliance



[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	<p>Current ECHA Candidate List: JAN 2025 (247)</p> <p>Candidate List Declared Against: JAN 2024 (240)</p> <p>SVHC &gt; Threshold:</p> <p>Pb (3.7% in Component Part)</p> <p><b>Article Safe Usage Statements:</b>                      Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</p>
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


### Customers Also Bought



TE Part #50845-1  
TERMINAL,PIDG PTFE R 12-10 8




TE Part #87499-9  
05 MODIV HSG SR MRKD .100CL



TE Part #350373-1  
06P STR/REL HSG HNGD



TE Part #2-350377-0  
MR SPLT GROMET .156 DIA BLK LF



## Documents

### Product Drawings

#### 15 RCPT ACT PIN/MS SCRLK

English

### CAD Files

#### Customer View Model

[ENG\\_CVM\\_CVM\\_5786144-1\\_B.2d\\_dxf.zip](#)

English

#### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_5786144-1\\_B.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_5786144-1\\_B.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Product Specifications

#### Application Specification

English

### Agency Approvals

#### UL Report

English