




			1 SE
Product designation			SLIM RELAY
Product type designation			HR20
Contact characteristics			
Contact configuration			1 Static
Rated insulation voltage Ui IEC/EN		V	2500
Nated insulation voltage of IEC/EN		V	(input/output)
IEC Conventional free air thermal current Ith		Α	2
Maximum instantaneous current		Α	80 (10ms)
Rated current (In)		Α	2
Relay control voltage		V	24VDC
Max contrallable power in			
	AC-1	W	1500
	AC-15	VA	360
Rated operating power AC-1			
			2A output 24
		VA	280VAC
Rated operating power AC-15			
· · · · · · · · · · · · · · · · · · ·	000 \ / 4 0		2A output 24
	230 VAC	VA	280VAC
Single-phase motor control			
	000) / 4 0	1.147	2A output 24
	230VAC	kW	280VAC
Rated operating current DC-1			
	001/		2A output 24
	30V	Α	280VAC
	110V	٨	2A output 24
	1100	Α	280VAC
	220V	Α	2A output 24
	220 V		280VAC
Minimum switching load		V / mA	24 / 0.1
Operating times			
Closing		ms	10
Opening		ms	10
Operations			
Mechanical life		cycles	Theoretically
		Cyclos	infinite
Electrical life AC1		cycles	Theoretically
		0,0100	infinite
Coil characteristics			
Operating range			
	Closing	% Un	80120
Maximum cycle frequency		cycles/h	>100000
Mechanical features			
Max socket terminal tightening torque		Nm	0.5
Socket screw tightening tool (cross / flat blade)			PH0 / 3.5mm
Conductor section			




	101		
$\Lambda \Lambda \Lambda$	112/	Kcr	nıl
\neg	10/	NO	

		min		20
		max		16
	IEC			_
		min	mm²	0.5
		max	mm²	1.5
Operating position				
		normal		Any
Fixing				On 35mm DIN rail
Ambient conditions				
Temperature				
	Operating temperature			
		min	°C	-30
		max	°C	+80
	Storage temperature			
		min	°C	-30
		max	°C	+100
Other features				
Indication				Yes (on the socket)
Mechanical contact po	osition indicator			No
Mechanical test actuat	tor			No
Dimensions				

Dimensions




PCB layout



Wiring diagrams





Certifications and compliance

Compliance

IEC/EN 62314

Certificates

cURus

TÜV-SUD

ETIM classification

ETIM 8.0

EC002055 -Solid state relay