



Application	Commercial, Education, Healthcare, Hospitality, Retail
Specification	Architectural

Vasco EVO

Vasco EVO CCT Multi Wattage 1200mm Black
Code: AVAS4/1/B



Varied Mounting Options
Flexible installation with surface, suspension,
track and wall mounting options available



PRODUCT FEATURES

- Aluminium bi-directional suspended or surface linear suitable for education, commercial and retail applications
- High efficiency upto 150lm/W (only when fitted with UGR diffuser - AVAS4/1/UGR)
- CCT selectable between 3000K and 4000K and power selectable; offering a choice of 2 outputs, in one luminaire
- Pre-wired with 1.5 metre cable
- Bi-directional light output as standard with 30% upward light and 70% downward light ratio (downward only option can be selected if required, please note light output changes in downward only mode)
- Opal diffuser (provided as standard) provides optimal light uniformity
- PIR end cap accessory available
- Adjustable suspension points c/w suspension kit

GENERAL INFORMATION

Wattage	14W - 32W
Lumens Delivered	1500lm - 3400lm (4000K) / 2000lm - 4600lm (4000K w/ AVAS4/1/UGR)
Lm/W	105lm/W (150lm/W w/ AVAS4/1/UGR)
Beam Angle	110
CRI	80
CCT	3000K/4000K
Input	220-240V
Operating Temp	-20°C to 45°C
SDCM	3
UGR	23
Product Weight without Packaging	2.74 kg

TECHNICAL INFORMATION

Light Source	LED
Colour / Finish	Black
IP Rating	IP40
IK Rating	IK06
Class Protection	1
Internal / External	Internal
Surface / Recessed / Suspended	Surface, Suspended
Lumen Depreciation	L80 100,000h
Warranty (Years)	5
CE Mark	Yes
Height	75 mm







Application	Commercial, Education, Healthcare, Hospitality, Retail
Specification	Architectural

Vasco EVO

Vasco EVO CCT Multi Wattage 1200mm Black
Code: AVAS4/1/B



ACCESSORIES

AVAS/1/1200/B	Vasco EVO Infill 1200mm Black
AVAS4/1/UGR	Vasco EVO UGR19 Reflector 1200mm
AVASLED/B/SK	Vasco CCT Suspension Kit Black
AVASLED/90/B	Vasco CCT 90° Corner Connector Black
AVAS/WM/1	Vasco Wall Mounting Kit
AVAS/P3/2/B	Vasco Three Circuit Track Adaptor Black

