



Cut protection

KRYTECH 836

High risk - ISO D



CUT PROTECTION
LEVEL D



ISO 13997:
17.2 N

DEXTERITY
EN ISO 21420:
3/5

Excellent cut protection and resistance to wear with optimal dexterity and comfort.

SPECIFIC ADVANTAGES



Cut protection

- Excellent cut resistance on all parts of the glove. Reinforced protection of the fore-arm thanks to its longer cuff.

Puncture protection

- Good resistance to wear and good puncture resistance (barbs) due to leather palm.



Durability

- Reinforced crotch between thumb and forefinger



Guaranteed quality

- Silicone free to prevent traces, defects on metal sheet and glass prior to painting



Washability

- Dry cleaning: Up to 5 times to extend glove lifespan, reduce costs and waste

INDUSTRIES

- Automotive/mechanical industry

APPLICATIONS

- Cutting strips (plasma etc.)
- Handling parts post-press
- Handling sheet metal
- Handling untrimmed parts or sheet metal
- Metal working



Cut protection

KRYTECH 836

High risk - ISO D

LEGENDS

EN388		MECHANICAL HAZARDS					
		PERFORMANCE LEVELS (X = NOT TESTED)					
4	X	4	3	D			
0-4	0-5	0-4	0-4	A-F	P		
						Impact protection (optional)	
						Cut resistance according to ISO 13997	
						Puncture resistance	
						Tear resistance	
						Blade cut resistance	
						Abrasion resistance	

EN407		THERMAL RISKS (HEAT AND FIRE)					
		PERFORMANCE LEVELS (X = NOT TESTED)					
X	1	X	X	X	X		
0-4	0-4	0-4	0-4	0-4	0-4		
						Resistance to large quantities of molten metal	
						Small splashes of molten metal	
						Radiant heat resistant	
						Convective heat resistance	
						Contact heat resistance	
						Limited flame spread	

PRODUCT DETAILS

Interior finish	Seamless textile support from HDPE fibres
Gauge	13
Exterior finish	Leather layer on palm with reinforced thumb / index
Cuff characteristic	Knitted Cuff
Colour.s	Grey
European sizes	7 8 9 10 11

LOGISTIC DETAILS

Packaging	1 pair/bag 12 pairs/bag 48 pairs/carton
-----------	---

LEGISLATION

- This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council.
- This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).
- UE type certificate or CE type examination certificate: 0075/014/162/03/19/0881
- Issued by the notified body nr: 0075 CTC - 4, rue Hermann Frenkel - 69367 Lyon Cedex 07- FRANCE