

SITOP PSU100S 12 V/7 A
 SITOP PSU100S 12 V/7 A Stabilized power supply input: 120/230 V
 AC, output: 12 V DC/7 A



Input	
Input	1-phase AC
• Note	Automatic range selection
Supply voltage	
• 1 at AC Rated value	120 V
• 2 at AC Rated value	230 V
Input voltage	
• 1 at AC	85 ... 132 V
• 2 at AC	170 ... 264 V
Wide-range input	No
Oversvoltage resistance	2.3 × Vin rated, 1.3 ms
Mains buffering	at Vin = 93/187 V
Mains buffering at lout rated, min.	20 ms; at Vin = 93/187 V
Rated line frequency 1	50 Hz
Rated line frequency 2	60 Hz
Rated line range	47 ... 63 Hz
Input current	
• at rated input voltage 120 V	1.73 A
• at rated input voltage 230 V	0.99 A

Switch-on current limiting (+25 °C), max.	45 A
Built-in incoming fuse	T 3,15 A/250 V (not accessible)
Protection in the mains power input (IEC 898)	Recommended miniature circuit breaker: from 6 A characteristic C

Output

Output	Controlled, isolated DC voltage
Rated voltage Vout DC	12 V
Total tolerance, static ±	3 %
Static mains compensation, approx.	0.1 %
Static load balancing, approx.	1 %
Residual ripple peak-peak, max.	150 mV
Residual ripple peak-peak, typ.	20 mV
Spikes peak-peak, max. (bandwidth: 20 MHz)	240 mV
Spikes peak-peak, typ. (bandwidth: 20 MHz)	100 mV
Adjustment range	11.5 ... 15.5 V
Product function Output voltage adjustable	Yes
Output voltage setting	via potentiometer
Status display	Green LED for 12 V OK
Signaling	Relay contact (NO contact, rating 60 V DC/ 0.3 A) for 12 V OK
On/off behavior	Overshoot of Vout < 3 %
Startup delay, max.	0.3 s
Voltage rise, typ.	10 ms
Rated current value Iout rated	7 A
Current range	0 ... 7 A
• Note	+50 ... +70 °C: Derating 0.75%/K
Supplied active power typical	84 W
Short-term overload current	
• on short-circuiting during the start-up typical	25 A
• at short-circuit during operation typical	25 A
Duration of overloading capability for excess current	
• on short-circuiting during the start-up	800 ms
• at short-circuit during operation	800 ms
Parallel switching for enhanced performance	Yes
Numbers of parallel switchable units for enhanced performance	2

Efficiency

Efficiency at Vout rated, Iout rated, approx.	84 %
Power loss at Vout rated, Iout rated, approx.	15 W

Closed-loop control

Dynamic load smoothing (Iout: 10/90/10 %), Uout ± typ.	5 %
Load step setting time 10 to 90%, typ.	1 ms
Load step setting time 90 to 10%, typ.	1 ms

Protection and monitoring	
Output overvoltage protection	< 20 V
Current limitation	7 ... 8.8 A
Property of the output Short-circuit proof	Yes
Short-circuit protection	Constant current characteristic
Enduring short circuit current RMS value <ul style="list-style-type: none"> • typical 	8.8 A
Overcurrent overload capability in normal operation	overload capability 150 % I _{out} rated up to 5 s/min
Overload/short-circuit indicator	-

Safety	
Primary/secondary isolation	Yes
Galvanic isolation	Safety extra-low output voltage U _{out} acc. to EN 60950-1 and EN 50178
Protection class	Class I
Leakage current <ul style="list-style-type: none"> • maximum • typical 	3.5 mA 0.4 mA
Degree of protection (EN 60529)	IP20

Approvals	
CE mark	Yes
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259, cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)
Explosion protection	IECEx Ex nA nC IIC T4 Gc; ATEX (EX) II 3G Ex nA nC IIC T4 Gc; cULus Class I Div. 2 (ANSI/ISA-12.12.01-2007, CSA C22.2 No. 213) Group ABCD, T4; cCSAus (CSA C22.2 No. 213, ANSI/ISA-12.12.01) Class I, Div. 2, Group ABCD, T4
FM approval	-
CB approval	Yes
Marine approval	DNV GL

EMC	
Emitted interference	EN 55022 Class B
Supply harmonics limitation	EN 61000-3-2
Noise immunity	EN 61000-6-2

environmental conditions	
Ambient temperature <ul style="list-style-type: none"> • during operation — Note • during transport • during storage 	-25 ... +70 °C with natural convection -40 ... +85 °C -40 ... +85 °C
Humidity class according to EN 60721	Climate class 3K3, 5 ... 95% no condensation

Mechanics

Connection technology	screw-type terminals
Connections	
<ul style="list-style-type: none"> • Supply input • Output • Auxiliary • signaling contact 	<p>L, N, PE: 1 screw terminal each for 0.5 ... 2.5 mm² single-core/finely stranded</p> <p>+, -: 2 screw terminals each for 0.5 ... 2.5 mm²</p> <p>Alarm signals: 2 screw terminals for 0.5 ... 2.5 mm²</p> <p>2 screw terminals for 0.5 ... 2.5 mm²</p>
Width of the enclosure	50 mm
Height of the enclosure	125 mm
Depth of the enclosure	120 mm
Required spacing	
<ul style="list-style-type: none"> • top • bottom • left • right 	<p>50 mm</p> <p>50 mm</p> <p>0 mm</p> <p>0 mm</p>
Weight, approx.	0.5 kg
Product feature of the enclosure housing for side-by-side mounting	Yes
Installation	Snaps onto DIN rail EN 60715 35x7.5/15
MTBF at 40 °C	1 998 441 h
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)