

FEATURES

- **LED Display:** Provides clear visibility of temperature settings for precise control
- **Input Voltage 120 – 230 V:** Compatible with a wide range of power supplies
- **Single Output:** Simplifies operation with a dedicated output for soldering tasks
- **Type G and Type E Plug Options:** Offers versatility for use in different regions
- **80W Power Rating:** Ensures rapid heating and consistent performance
- **500°C Soldering Tip Temperature:** Suitable for a variety of soldering applications

RS PRO 80W Soldering Station, 500°C Temperature

RS Stock No: 631-068



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO 80W Soldering Station is designed for precision soldering tasks, offering reliable performance for both professional and hobbyist applications. With a maximum temperature of 500°C, it ensures efficient soldering of various electronic components, making it ideal for detailed work.

General Specifications

Display Type	LED
Number of Outputs	1
Product Type	Soldering Station
Soldering Tip Temperature	500 °C
Tasks Supported	Soldering

Protection Category

ESD Safe	No
----------	----

Electrical Specifications

Input Voltage	120-230 V
Plug Type	Type G - British 3-Pin, Type E - France-2 Round Pin
Power Rating	80 W

Approvals

Standards/Approvals	CE, UKCA
---------------------	----------