

Article No. : 1FL2306-7AC11-1SB0



Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :


Basic motor data	
Motor type	Permanent-magnet synchronous motor
Motor type	High Inertia
Static torque	13.30 Nm
Static current	7.80 A
Maximum torque	33.43 Nm
Maximum current	20.7 A
Maximum speed	3,000 rpm
Rotor moment of inertia	29.9380 kgcm ²
Weight	16.7 kg

Rated data	
SINAMICS S200, 3 AC 380 ... 480 V	
Rated speed	2,000 rpm
Rated torque	9.60 Nm
Rated current	5.9 A
Rated power	2.00 kW

Encoder system	
Encoder system	Absolute encoder singleturn 21 bit

Motor connection	
Connection type	Metal angular connector

Mechanical data	
Design acc. to Code I	IM B5 (IM V1, IM V3)
Vibration severity grade	Grade A
Shaft height	65
Flange size (AB)	130 mm
Centering ring (N)	110 mm
Hole circle (M)	145 mm
Screw-on hole (S)	9.0 mm
Overall length (LB)	301.7 mm
Diameter of shaft (D)	22 mm
Length of shaft (E)	58 mm
Length of flange diagonal (P)	165.2 mm
Shaft end	Shaft with parallel key (half-key balancing)
Color of the housing	Anthracite RAL 7016



Holding brake	
Rated voltage	24 V DC 10 %
Rated current	1.50 A
Holding torque M _{4Br}	12.00 Nm
Opening time	180 ms
Closing time	60 ms