


Fail-safe inductive sensor

GIK4008B2PS/SIL2/AM/US



Product characteristics

Electrical design	PNP
Enable zone [mm]	0...6
Housing	threaded type
Dimensions [mm]	M30 x 1.5 / L = 65

Application

Special feature	Gold-plated contacts; Full-metal housing
Type of operation	permanent operation
Safety-related sub-function	safe state when undamped correctly (s > sAs (sar))
Application	Use in mobile and harsh applications

Electrical data

Operating voltage [V]	9...32 DC
Rated insulation voltage [V]	60
Current consumption [mA]	< 10; (24 V)
Protection class	III
Reverse polarity protection	yes
Max. power-on delay time [ms]	500

Outputs

Electrical design	PNP
Max. voltage drop switching output DC [V]	2.5
Number of OSSD outputs	2
Max. current load per OSSD output [mA]	50
Output data	Interface type C class 1
Output voltage at 24 V	compatible with EN 61131-2 inputs type 1, 2
Short-circuit protection	yes
Overload protection	yes
Max. capacitive load CL_max [nF]	20



Fail-safe inductive sensor

GIK4008B2PS/SIL2/AM/US

Detection zone		
Enable zone	[mm]	0...6
Safe switch-off distance sAs (sar)	[mm]	18
Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.8 / aluminium: 0.6 / copper: 0.3
Response times		
Response time when approaching the enable zone, turn-on time (ton)	[ms]	20
Response time to safety request, turn-off time (toff)	[ms]	20
Risk time / error handling time (toff max)	[ms]	100; (at ambient temperature <-25 °C: 250 ms; flush mounting with a single stainless steel fixing nut: 250 ms)
Operating conditions		
Ambient temperature	[°C]	-40...85
Max. height above sea level	[m]	3000
Ionising radiation		not permissible
Protection		IP 65; IP 66; IP 67; IP 68; IP 69K
Tests / approvals		
EMC	industrial environments	
	EN 60947-5-3	
	EN 61000-4-2 ESD	6 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	20 V/m 80...1000 MHz
	EN 61000-4-3 HF radiated	10 V/m 1,4...2,0 GHz / 3 V/m 2,0...6,0 GHz
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-5 Surge	2 kV
	EN 61000-4-6 HF conducted	10 V
	EN 61000-4-8	30 A/m 50/60 Hz / 1000 A/m 0 Hz
	EN 55011	class B
	mobile applications	only for operation with central load-dump suppression (58 V) / not for active operation during motor start phase in 12 V systems
	ISO 10605 ESD	8 kV CD / 15 kV AD
	ISO 11452-2, ISO 11452-5 radiated immunity	100 V/m 400...3000 MHz
	ISO 7637-2, ISO 16750-2 conducted immunity	12 V / 24 V
	pulse	1 2a 2b 3a 3b 4 5b
	severity level	III III III III III III 58V
	failure criterion	B A B A A C/B A/C
	EN 55025	class 3
Shock resistance	EN 60068-2-27 Ea	100 g 11 ms half-sine; 3 shocks each in every direction of the 3 coordinate axes
Continuous shock resistance	EN 60068-2-27 Ea	40 g 6 ms; 4000 shocks each in every direction of the 3 coordinate axes
Fast temperature change	EN 60068-2-14 Na	TA = -40°C; TB = 85°C; t1 = 45 min; t2 = 10 s 100 cycles



Fail-safe inductive sensor

GIK4008B2PS/SIL2/AM/US

Vibration resistance	EN 60068-2-6 Fc	20 g (10...3000 Hz) / 50 sweep cycles, 1 octave per minute, in 3 axes
	EN 60068-2-64 Fh	5.9 g RMS / effective acceleration for chassis mounting
	ISO 19014-3	5.7 g RMS / effective acceleration
Salt spray test	EN 60068-2-52 Kb	severity level 5 (4 test cycles)
UL approval	Ta	-40...70 °C
	Enclosure type	Type 1
	power supply	Limited Voltage/Current
	UL approval no.	A064
	File number UL	E174191

Safety classification

Complies with the requirements	ISO 13849-1 category 2, PL d
	IEC 61508 SIL 2, HFT 0, SC 2
Mission time TM [h]	≤ 87600
Mission time TM (additional indication)	industrial environments Temperature range -25...70 °C ≤ 175200
PFH [1/h]	< 1,5E-07

Mechanical data

Weight [g]	134.1
Housing	threaded type
Mounting	flush mountable
Dimensions [mm]	M30 x 1.5 / L = 65
Thread designation	M30 x 1.5
Materials	threaded sleeve: stainless steel (316L/1.4404); sensing face: stainless steel (316L/1.4404); LED window: PEI; LED Sealing: PU; lock nuts: stainless steel (316L/1.4404)
Tightening torque [Nm]	70
Full-metal housing	yes

Displays / operating elements

Display	Display switching status	4 LED, yellow
---------	--------------------------	---------------

Accessories

Items supplied	lock nuts: 2
----------------	--------------

Remarks

Remarks	meets the environmental and EMC requirements for operation in agricultural and forestry machinery, earthworks and construction machines as well as in industrial trucks
	can be used in applications up to SIL 2 in accordance with IEC 62061, MPL d in accordance with ISO 19014-3 and Ag PL d in accordance with ISO 25119
	Unless stated otherwise, all data refer to the reference target plate to IEC 60947-5-2 over the whole temperature range.
	(FE360 = ST37-2K) 30x30x1 mm
	the correction factors apply to an ambient temperature of 20°C
	do not use a correction factor for the safe switch-off distance sAs/(sar)
Pack quantity	1 pcs.

GI761S



Fail-safe inductive sensor


GIK4008B2PS/SIL2/AM/US

Electrical connection - plug

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection



1	L+
2	OSSD2
3	L-
4	OSSD1