

## Description

STAINLESS STEEL TOP PLATE CASTOR, RED POLYURETHANE 125MM

### Fixed

**KF41BA125-28L**



### Part Number

#### Swivel

**KP41BA125-28L**




#### Swivel and brake

**KP41BD125-28L**



	Fixed	Swivel	Swivel+brake
Wheel Diameter ØD	125 mm		
Overall Height H	155 mm ±1		
Size of plate A X B	105 x 85 mm±1		
Plate hole centres a x b	80 x 60 mm±0,3		
Plate hole	9 mm		
Offset F ±1	\	38 mm	38 mm
Width of Tread	35 mm±0,5		
Hardness of tread	shore A ± 98		
Load capacity	200 Kg		
Weight	0,70 kg	0,83 kg	1,05 kg
Temperature	- 20 / + 60 °C		



### Castor Assembly :

Pressed stainless steel -AISI 304-. Swivel on two rows of balls.  
Fastening by top plate.  
Total lock. Metal pedal.

### Wheel :

Wheel centre made of White Polyamide.  
Tread : Red injected Polyurethane non marking.  
Hub : Plain bore.

### Features :

Low starting effort. High load capacity.  
Lightweight, highly resistant to knocks and other impacts, abrasion as well as a great many chemical substances.  
Corrosion resistant, easy to clean. Specially designed for humid environments.  
Suited for Food industry, Hospital or Industrial Kitchen equipment.  
Non staining red tyre.  
Medium duty.