

RF-12P1N8AAD00 - Device connector front mounting



1607233

<https://www.phoenixcontact.com/gb/products/1607233>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector front mounting, angled rotatable, Screw locking mechanism, M23, number of positions: 12, contact connection type: Pin, Axial O-ring, shielded: yes, flange dimensions: 26 mm x 26 mm, number of positions: 12, connection method: Crimp connection, series: RF

Your advantages

- Easy connection, thanks to infinitely adjustable cable outlet direction up to 310°
- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable connection solutions in the industrial environment
- Crimping connection: vibration- and temperature-resistant assembly

Commercial data

Item number	1607233
Packing unit	16 pc
Minimum order quantity	1 pc
Sales key	ABRAGM
Product key	ABRAGM
Catalog page	Page 112 (C-2-2019)
GTIN	4046356175012
Weight per piece (including packing)	132.8 g
Weight per piece (excluding packing)	117.019 g
Customs tariff number	85366990
Country of origin	DE

RF-12P1N8AAD00 - Device connector front mounting



1607233

<https://www.phoenixcontact.com/gb/products/1607233>

Technical data

Notes

Order information:	Order crimp contacts Ø 1 mm separately
--------------------	--

Mounting

Mounting type	Front mounting/square flange 4x Ø 3,2 mm
Assembly note	4x Ø 3,2 mm

Product properties

Product type	Circular connectors (device side)
Series	RF
Application	Signal
	Signal
Number of positions	12
Connection profile	12
Shielded	yes
Coding	N
Thread type	M23

Dimensions

Housing

Flange dimensions	26 mm x 26 mm
-------------------	---------------

Material specifications

Seal material	FPM
Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Insulator material	PA 6.6
Gasket and O-ring material	FPM

Electrical properties

Contact

Contact diameter	1 mm
Max. current	8 A
Nominal voltage U _N	48 V AC 74 V DC
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV

Connection data

Conductor connection

Connection method	Crimp connection
-------------------	------------------

RF-12P1N8AAD00 - Device connector front mounting



1607233

<https://www.phoenixcontact.com/gb/products/1607233>

Contact connection type	Pin
-------------------------	-----

Connector

Type	angled rotatable
Direction of rotation	Standard


Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 125 °C
Altitude	2000 m


Drawings

Dimensional drawing



Dimensional drawing

Dimensional drawing




Installation dimensions

1607233

<https://www.phoenixcontact.com/gb/products/1607233>

Schematic diagram



Contact chamber numbering (view of plug-in side), standard pin

RF-12P1N8AAD00 - Device connector front mounting



1607233

<https://www.phoenixcontact.com/gb/products/1607233>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1607233>

cUL Recognized Approval ID: E153698-20090723				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
	48 V	5 A	20	-

UL Recognized Approval ID: E153698-20090723				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
	48 V	5 A	20	-

RF-12P1N8AAD00 - Device connector front mounting



1607233

<https://www.phoenixcontact.com/gb/products/1607233>

Classifications

ECLASS

ECLASS-13.0	27440109
-------------	----------

ETIM

ETIM 9.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

RF-12P1N8AAD00 - Device connector front mounting



1607233

<https://www.phoenixcontact.com/gb/products/1607233>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk