

## Plastic label - EMLP (45X25)R - 0802727

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Plastic label, Roll, white, unlabeled, can be labeled with: THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK X1.2, Mounting type: Adhesive, Lettering field: 45 x 25 mm


The figure shows a similar product

### Why buy this product

- ✓ Quick and cost-effective labeling with THERMOMARK ... printers
- ✓ High level of resistance to chemical and mechanical influences
- ✓ High-quality appearance
- ✓ The EMLP ... self-adhesive markers are equivalent to engraved labels
- ✓ Primarily used for marking electrical components, devices, and buttons



### Key commercial data

Packing unit	1
GTIN	 4 046356 845885
Custom tariff number	39199000

### Technical data

#### Dimensions

Length (b)	45 mm
Width (a)	25 mm

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Ambient temperature (assembly)	18 °C ... 40 °C
Recommended storage conditions	21 °C / 50 % relative humidity.

#### General

Color	white
Components	free from silicone and halogen
Inflammability class according to UL 94	V0
Material	Polyester

# Plastic label - EMLP (45X25)R - 0802727

## Technical data

### General

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	500
Number of individual labels per row	1
Adhesive	Acrylic
Printability	Thermal transfer
Device	5146477 THERMOMARK ROLL
	5146723 THERMOMARK ROLL X1
	5146257 THERMOMARK S1.1
	5146231 THERMOMARK X1.2
Ink ribbon	5145384 THERMOMARK-RIBBON 110
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	Following DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 60068-2-11:2000-02
Result	Test passed
Foil strength	50 µm
Adhesive strength	20 µm
Marking mounting type	Adhesive

## Classifications

### eCl@ss

eCl@ss 4.0	24190218
eCl@ss 4.1	24190218
eCl@ss 5.0	27141137
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137

### ETIM

ETIM 3.0	EC000761
ETIM 4.0	EC000761

## Plastic label - EMLP (45X25)R - 0802727

### Classifications

#### ETIM

ETIM 5.0	EC000761
----------	----------

#### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410