



Connectors > Pluggable IO Connectors & Cages



Form Factor: **QSFP28/56**
Pluggable I/O Product Type: **Cage Assembly**
Sealable: **No**
Circuit Application: **Signal**
Operating Temperature Range: **-40 – 85 °C [-40 – 185 °F]**

Features

Product Type Features

Cage Type	Ganged
Thermal Accessory Type Included	Heat Sink
Form Factor	QSFP28/56
Pluggable I/O Product Type	Cage Assembly
Sealable	No

Configuration Features

Number of Rear EONs per Port Column	1
Number of Ports	3
Port Matrix Configuration	1 x 3

Electrical Characteristics

Data Rate (Max)	28 Gb/s
-----------------	---------

Body Features

Heat Sink Style	Pin
Heat Sink Finish	Anodized Black
	.531 in
Heat Sink Height Class	Networking

Contact Features

PCB Contact Termination Area Plating Material	Tin
---	-----



Termination Features

Termination Method to PCB	Through Hole - Press-Fit
Termination Post & Tail Length	2.05 mm[.081 in]

Housing Features

Cage Material	Nickel Silver
---------------	---------------

Dimensions

PCB Thickness (Recommended)	1.57 mm[.062 in]
-----------------------------	------------------

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Pluggable I/O Applications	SFP+ Stacked Belly-to-Belly
Circuit Application	Signal

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Box & Tray
------------------	------------

Other

Included Lightpipe	Yes
EMI Containment Feature Type	Internal/External EMI Springs

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # CAT-C11-Z8 QSFP28 to QSFP28 Cable Assembly: 26 AWG	 TE Part # CAT-Q17-N49033 QSFP56-Two QSFP56 Cable Assembly: 30 AWG	 TE Part # CAT-C11-Q17 QSFP56 to QSFP56 Cable Assembly: 26 AWG	 TE Part # 1888810-2 EMI/Dust Cover,XFP And QSFP
 TE Part # 1551920-2 zQSFP+ connector assembly	 TE Part # CAT-Q17-N490325 QSFP56 to QSFP56 Cable Assembly: 30 AWG	 TE Part # CAT-Q17-N490333 QSFP56-Four SFP56 Cable Assembly: 26 AWG	 TE Part # CAT-C11-N490333 QSFP28-Four SFP+ Cable Assembly: 30 AWG
 TE Part # CAT-C11-N49 QSFP28-Two QSFP28 Cable Assembly: 30 AWG	 TE Part # CAT-C11-N490325 QSFP28-Four SFP+ Cable Assembly: 26 AWG	TE Part # 3-2215047-3 ASSY, STG TL, QSFP28 LP,1X3	 TE Part # CAT-C11-Z806726 QSFP28 to QSFP28 Cable Assembly: 30 AWG



TE Part # CAT-Q17-N49011
QSFP56-Four SFP56 Cable Assembly:
30 AWG

Also in the Series | **zQSFP+/QSFP28**



Heat Sinks(7)




Pluggable IO Connectors & Cages(424)



QSFP, QSFP+ & zQSFP+(424)

Customers Also Bought




TE Part #3-1775099-3
ATX PWR CONN 1 BDLK 10 POS



TE Part #2170872-1
Z-PACK TYPE/C MALE HDR 55P



TE Part #6-1658043-2
MSB0.80RC-ASY080FL,GP,F,-TR



TE Part #3-1775099-5
ATX PWR CONN 1 BDLK 14 POS



TE Part #2132423-1
IMP100O,R,RA3P6C,RG,39



TE Part #5-2170790-4
CAGE ASSY, 1X4, QSFP28, SPRING,
HS, LP



TE Part #1934937-1
Tinman 5pr 10col open hdr assy



TE Part #6450834-1
MBXL R/A HDR STR 1P/8S/1P



TE Part #2-2204910-5
MBXLE R/A HEADER 4HDP + 92S +
4HDP



TE Part #2007850-1
IMP100S,H,V5P10C,UG,DEW46,4.5



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_4-2170740-3_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_4-2170740-3_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_4-2170740-3_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

QSFP28/56 and zQSFP+ Interconnects

English

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English