


Product data sheet

Specifications



Repacked, load-shedding contactor, Acti9 CDS, 3 C, white

A9C15913W



This repacked option saves 4.464 over the standard condition

Main

range of product	Acti9
Product name	Acti9 CDS
Product or component type	Load-shedding contactor
Device short name	CDS
Number of channels	3
Control and monitoring type	Independant phase control
Poles description	3P

Complementary

Setting	70 30 40 60 15 25 10 80 20 5 90 50
Power consumption in VA	12 VA
[Ue] rated operational voltage	415 V AC - 15...10 % at 50/60 Hz
Rated current	15 A for non-priority circuit Adjustable from 5 to 90 A for priority circuit
Local signalling	Load-shedding indication: 3 LEDs (yellow)
Mounting support	35 mm symmetrical DIN rail Wall mounted Panel mounting
9 mm pitches	16
Connections - terminals	Non-priority circuit: screw terminal2.5...10 mm² flexible Non-priority circuit: screw terminal2.5...10 mm² rigid Priority circuit: screw terminal10...35 mm² flexible Priority circuit: screw terminal10...50 mm² rigid
IP degree of protection	IP20 conforming to IEC 60529
Height	77 mm
Width	144 mm
Depth	60 mm
Product weight	0.5 kg
Colour	White (RAL 9003)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Tightening torque	Non-priority circuit: 2 N.m Priority circuit: 3.5 N.m
Wire stripping length	12 mm 13 mm

Environment

Standards	NF C 61-750 EN 50081-1 EN 50081-2
Ambient air temperature for operation	-5...55 °C
Ambient air temperature for storage	-40...70 °C
Tropicalisation	2 conforming to IEC 60068-1
Relative humidity	95 % at 55 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.700 cm
Package 1 Width	11.500 cm
Package 1 Length	15.500 cm
Package 1 Weight	506.000 g
Unit Type of Package 2	S02
Number of Units in Package 2	6
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	3.341 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

4 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard

No

Packaging without single use plastic

No

SCIP Number

429095ee-388a-4184-bea4-16f87e374975

EU RoHS Directive

[Compliant By Exemption](#)

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

Take-back

No

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins