



# Technical Datasheet

## Dräger X-plore 8000

### Earmuffs

---

## 1. General Data

1.1	Manufacturer	Dräger Safety AG & Co. KGaA Revalstraße 1, D – 23 560 Luebeck, Germany	
1.2	Designation	Dräger X-plore 8000 Earmuffs	
1.3	Dräger part no.	3710777	
1.4	GTIN / EAN	04048675668305	
1.5	Intended use	The Dräger X-plore® 8000 Earmuffs can only be used in combination with the X-plore 8000 helmet PC visor, helmet for hood and bump cap for hood.	
1.6	Functional description	<b>Helmet PC Visor:</b>	3710775, 3710780; 3710785, 3710790, 3710795
		<b>Helmet for hood:</b>	3710800
		<b>Bump Cap for:</b>	3710805
1.7	Approvals	EN 352-3:2002 ANSI S3.19-1974 EU 2016/425	

## 2. Technical Data

2.1	Materials	
	Housing	ABS (Acrylonitrile butadiene styrene)
	Padding	EVA (Ethylene vinyl acetate)
	Sealing cushions	PVC (Polyvinyl chloride)
	Holding brackets	Nickel-plated spring steel
2.2	Protection class	SNR 33dB; H 37dB; M 30dB; L 23dB
2.3	Weight	220 g
2.4	Colour	Grey
2.5	Storage temperature	Max. 55°C
2.6	Cleaning	Wipe the Earmuffs with a soft cloth and mild detergent allow earmuffs to air dry. Protect from direct sunlight.

### 3. Documentation

3.1	Labelling	<p><b>The label contains the following information:</b></p> <ul style="list-style-type: none"><li>- Approval markings</li><li>- CE-mark</li><li>- UKCA-mark</li><li>- Symbol "Follow the instructions for use", "Storage conditions"</li><li>- Manufacturer</li><li>- Country of production ("Made in USA")</li><li>- Date of manufacture</li><li>- Part number</li></ul>
3.2	Instructions for use	<p><b>Each packaging unit contain instructions for use in the following languages:</b></p> <p>English, German, French, Spanish, Italian, Dutch, Danish, Polish</p> <p><b>The instructions for use for the following languages are available online:</b></p> <p>Bulgarian, Chinese, Estonian, Finnish, Greek, Japanese, Korean, Croatian, Hungarian, Latvian, Lithuanian, Norwegian, Portuguese, Romanian, Russian, Swedish, Slovak, Slovenian, Serbian, Thai, Czech, Turkish</p>

4. Other

4.1. User instructions and restrictions	The product meets the minimum requirements according to the standard according to the specified class and type (see labeling). It should be noted that laboratory test values may differ significantly from those achieved in practice. This may lead to longer or shorter durability. The user must read and understand all package leaflets. In addition, knowledge of all relevant application rules is absolutely necessary (especially the usage restrictions for filter devices). Further information are available upon request.
---	---

Mentioned Trademarks are only registered in certain countries and not necessarily in the country in which this material is released.  
Go to [www.draeger.com/trademarks](http://www.draeger.com/trademarks) to find the current status.


**Corporate Headquarters**  
Drägerwerk AG & Co. KGaA  
Moislinger Allee 53-55  
23558 Lübeck, Germany  
  
[www.draeger.com](http://www.draeger.com)

**Region Europe**  
Dräger Safety AG & Co. KGaA  
Revalstraße 1  
23560 Lübeck, Germany  
☎ +49 451 882 0  
☎ +49 451 882 2080  
✉ [info@draeger.com](mailto:info@draeger.com)

**Region Asia Pacific**  
Draeger Singapore Pte. Ltd.  
Science Park Road  
The Galen #04-01  
Singapore 117525  
☎ +65 6872 9288  
☎ +65 6259 0398

**Region Middle East, Africa**  
Dräger Safety AG & Co. KGaA  
Branch Office  
P.O. Box 505108  
Dubai, United Arab Emirates  
☎ +971 4 4294 600  
☎ +971 4 4294 699  
✉ [contactuae@draeger.com](mailto:contactuae@draeger.com)

**Region Central and South America**  
Dräger Indústria e Comércio Ltda.  
Al. Pucurui - 51 - Tamboré  
06460-100 - Barueri - São Paulo  
☎ +55 (11) 4689-4900  
✉ [relacionamento@draeger.com](mailto:relacionamento@draeger.com)

 Locate your Regional Sales Representative at:  
[www.draeger.com/contact](http://www.draeger.com/contact)