



Application Tooling > Hand Crimping Tools



Tool Grade: **Premium Crimp Tooling**
Die Sets Type: **Removable/Interchangeable**
Specification Type: **MIL Spec, TE Product Specification (114-)**
TE Certification: **Yes – Certificate Included**
Power Technology Type: **Battery, Hydraulic, Manual**

Features

Other

Crimp Form-Wire Barrel Type	Closed Barrel - Confined Crescent
Tool Grade	Premium Crimp Tooling
Die Sets Type	Removable/Interchangeable
Specification Type	MIL Spec, TE Product Specification (114-)
TE Certification	Yes – Certificate Included
Power Technology Type	Battery, Hydraulic, Manual
Tooling Type	Die Assembly

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC

	Free
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 324083
TERMINAL,T-N R 2/0 5/16




TE Part # 69066
HYP8 8-4/0AWG 22T HEAD



TE Part # 324084
TERMINAL,T-N R 2/0 3/8



TE Part # 58422-1
HYP8 8-4/0AWG 33T HEAD



TE Part # 324085
TERMINAL,T-N R 2/0 1/2

Customers Also Bought



TE Part #2-1617805-5
TD228-5000P=TDFO .5 SEC M83726 /28-5000P




TE Part #1-1616058-4
A703FSS (FAA/PMA)=RELAY



TE Part #318460-001
55A6160-20-2/6-9-9



TE Part #CTJ120E04A-513
MODULE ASSY

<div></div> <div>TE Part #4-1616344-1 51204391=SCREW</div>	<div></div> <div>TE Part #1-1617033-0 HFW1206K03 = HFW 1/2 SIZE RELA</div>	<div></div> <div>TE Part #4-23619-8 PIN,STRAIGHT,GROOVED</div>	<div></div> <div>TE Part #269741N001 222F274-71-35-0-CS5860</div>
<div></div> <div>TE Part #650074N006 D-436-36CS454</div>	<div></div> <div>TE Part #813817N002 222D163-4-0-CS5354</div>		

Documents

Datasheets & Catalog Pages

AT-Hydraulic Crimp Tooling Solutions-1654519

English

Bottoming Dies

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English