




RoHS Compliant

REV	SIGN	DATE	DESCRIPTION	APPROVER
A		2023.12.19	Initial Release	Yours
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!				

- Material:
- Item ① Terminal Body: PA66,
 - Item ② Terminal lever: PBT,
 - Item ③ Terminal Cover: PA66,
 - Item ④ Spring: Stainless,
 - Item ⑤ Terminal Contact: Copper alloy,

- Electrical:
- | | | | | |
|--------------------------|-----------------|-----------|---------|---------|
| | UL1059 | Group B.G | Group D | Group F |
| ●Voltage rating: | 300 V | | 300V | 250V |
| ●Current rating: | 16A | | 10A | 16A |
| ●Wire range: | | | | |
| Solid wire: | 24-12AWG | | | |
| Stranded wire: | 24-12AWG | | | |
| ●Wire strip length: | 11-13 mm | | | |
| ●Withstanding Voltage: | 1.6KV AC | | | |
| ●Insulation Resisance: | DV500V 500MΩ | | | |
| ●Operating temperature: | -20°C to +105°C | | | |
| ●Assembling temperature: | -5°C to +105°C | | | |
| ●Safety Approval: | | | | |

Part No. QT xx A SF x x H xxxx G

- | | |
|-----------------------|---------------------------------------|
| NO. OF POLES | RoHS compliant |
| 02: 2 POLES | (lead<4%) |
| 03: 3 POLES | In copper Alloy |
| ... | |
| 24: 24 POLES | 00x0: "①" Logo (Standard) |
| | 00xA: "ANYTEK" Mark |
| | Any special item by customer request. |
| | please contact sales department. |
| Body color | Lever color |
| 0: Black | 0: Black |
| 1: Natural color | 1: Natural color |
| 2: Red | 2: Red |
| 3: Orange | 3: Orange (標準色) |
| 4: Yellow | 4: Yellow |
| 5: Green (RAL6018/T) | 5: Green (RAL6018/T) |
| 6: Blue | 6: Blue |
| 8: Grey (標準色) | 8: Grey |
| 9: White | 9: White |
| C: Green (RAL 6018/U) | C: Green (RAL 6018/U) |

Amphenol
ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		QT series pitch 5.0mm PCB terminal block,			
PART NO.	QTxxASFxxHxxxxG			DWG NO.	8QT0002
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance
Roy 2024.11.07	Roy 2024.11.07	Yours 2023.12.19	Yours 2023.12.19		X. ±0.50
					X.X ±0.30
					X.XX ±0.10
				SHEET: 01/01	REV.: A0
					X° ±1°