

Eaton 185672

Catalog Number: 185672

Eaton Moeller® series C22 Pushbutton, Flat, momentary, 1 NC, Cable (black) with non-terminated end, 4 pole, 1 m, black, Blank, Bezel: titanium

General specifications



Product Name	Catalog Number
Eaton Moeller® series C22 Pushbutton	185672
EAN	Product Length/Depth
4015081811663	1060 mm
Product Height	Product Width
30 mm	30 mm
Product Weight	Certifications
0.048 kg	CE
	IEC/EN 60947-5-1
	UL
	CSA
	VDE 0660
	CSA Class No.: 321103
	CSA File No.: 165628
	UL 508
	CSA-C22.2 No. 14-18 and No. 94.2-15
	CE marking
	UL Category Control No.: NKCR
	UL File No.: E29184

Product specifications

Type

Pushbutton actuator

Actuator color

Black

Features

Positive opening

Actuator function

Momentary

Spring-return

Electric connection type

Cable

Fitted with:

Front ring

Operating frequency

3600 Operations/h

Pollution degree

3

Climatic proofing

Damp heat, cyclic, to IEC 60068-2-30

Damp heat, constant, to IEC 60068-2-78

Connection to SmartWire-DT

No

Rated impulse withstand voltage (Uimp)

800 V AC

Bezel color

Titanium

Cable material

PUR

Actuating force

5 N

Actuator diameter

29.7 mm

Actuator travel and actuation force (DIN EN 60947-5-1)

4.65 mm

Ambient operating temperature - max

70 °C

Resources

Catalogs

[eaton-pushbuttons-signal-towers-sensors-assortment-overview-catalog-ca047003en-en-us.pdf](#)

Declarations of conformity

[DA-DC-00004135.pdf](#)

[DA-DC-00004157.pdf](#)

Drawings

[eaton-operating-c22-pushbutton-dimensions-004.eps](#)

[eaton-operating-devices-3d-drawing-170.eps](#)

[1160DRW-430](#)

[eaton-operating-button-symbol-005.eps](#)

eCAD model

[DA-CE-ETN.C22-D-S-K01-P62](#)

Installation instructions

[IL047016ZU](#)

Installation videos

[Eaton's RMQ compact solution pilot devices](#)

mCAD model

[DA-CS-c22_d_open_cable](#)

[DA-CD-c22_d_open_cable](#)

Sales notes

[eaton-rmq-mci-multi-color-light-indicator-flyer-fl047005en-en-us.pdf](#)

System overview

[Pilot devices - selection aid](#)

Wiring diagrams

[eaton-operating-c22-pushbutton-wiring-diagram.eps](#)

Ambient operating temperature - min

-30 °C

Force for positive opening - min

15 N

Knob travel

5.7 mm

Lamp voltage - max

0 V

Number of command positions

1

Number of contacts (change-over contacts)

0

Number of contacts (normally closed contacts)

1

Number of contacts (normally open contacts)

0

Bezel material

Plastic

Design

Flat

Classical

Mounting position

As required

Rated conditional short-circuit current (I_q)

1 kA

Connection type

Cable (black) with non-terminated end, 4 pole

Cable length

1 m

Overvoltage category

III

Control circuit reliability

1 failure per 900,000 switching operations statistically
determined, at 17 V DC/7 mA: N/C contact)

Degree of protection

NEMA 12

IP67/IP69K

Inscription

Blank

Front element type

Flat

Lens type

Round

Shock resistance

30 g, Mechanical, Shock duration 11 ms

Short-circuit protection rating

Max. 4 A gG/gL, Fuse, Contacts

Opening diameter

22.5 mm

Opening height

0 mm

Rated insulation voltage (Ui)

250 V

Rated operational current (Ie) at AC-15, 24 V

4 A

Rated operational current (Ie) at DC-13, 24 V

3 A

Width opening

0 mm

Product category

RMQ compact solution

Ambient storage temperature - max

80 °C

Ambient storage temperature - min

30 °C

Tightening torque

2 Nm, Threaded ring



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)