

Siemens
EcoTech



SIMATIC ET 200SP HA, digital input module, DI 8x230VAC HA suitable for terminal block K0, color code CC41, Module diagnostics

General information	
Product type designation	DI 8x230VAC HA
Firmware version	V1.0
<ul style="list-style-type: none"> FW update possible 	Yes
Color code for module-specific color-coded label	CC42
Product function	
<ul style="list-style-type: none"> I&M data 	Yes; I&M0 to I&M3
Engineering with	
<ul style="list-style-type: none"> STEP 7 TIA Portal configurable/integrated from version 	V16
<ul style="list-style-type: none"> STEP 7 configurable/integrated from version 	V5.6
<ul style="list-style-type: none"> PCS 7 configurable/integrated from version 	V9.0
<ul style="list-style-type: none"> PCS neo can be configured/integrated from version 	V3.0
<ul style="list-style-type: none"> PROFINET from GSD version/GSD revision 	GSDML V2.3
Operating mode	
<ul style="list-style-type: none"> DI 	Yes
Redundancy	
<ul style="list-style-type: none"> Redundancy capability 	No
Supply voltage	
Rated value (AC)	230 V
permissible range, lower limit (AC)	85 V
permissible range, upper limit (AC)	264 V
Power	
Power consumption from the backplane bus	105 mW
Power loss	
Power loss, typ.	1.8 W; Active power, load voltage 230 V, all inputs connected with 230 V, 50 Hz
Address area	
Address space per module	
<ul style="list-style-type: none"> Address space per module, max. 	1 byte; + 1 byte for QI information
Hardware configuration	
Automatic encoding	
<ul style="list-style-type: none"> Mechanical coding element 	Yes
Digital inputs	
Number of digital inputs	8; Isolated
Input characteristic curve in accordance with IEC 61131, type 3	Yes
Time stamp	Yes; Resolution 10 ms
Time stamp (with precision of 1 ms)	No

Input voltage	
• Rated value (AC)	230 V
• for signal "0"	0V AC to 40V AC
• for signal "1"	74 V AC to 264 V AC
Input current	
• for signal "1", typ.	10.8 mA
Input delay (for rated value of input voltage)	
for standard inputs	
— at "0" to "1", min.	1.5 ms
— at "0" to "1", max.	4 ms
— at "1" to "0", min.	10 ms
— at "1" to "0", max.	10 ms
Cable length	
• shielded, max.	1 000 m
• unshielded, max.	600 m
Encoder	
Connectable encoders	
• 2-wire sensor	Yes
Interrupts/diagnostics/status information	
Alarms	
• Diagnostic alarm	Yes
Diagnoses	
• Diagnostic information readable	Yes
Diagnostics indication LED	
• MAINT LED	Yes; Yellow LED
• Channel status display	Yes; green LED
• for module diagnostics	Yes; green/red DIAG LED
Potential separation	
Potential separation channels	
• between the channels	Yes
• between the channels, in groups of	2
• between the channels and backplane bus	Yes
Permissible potential difference	
between different circuits	Between channels: 230 V AC (same system phase) / 120 V AC (different system phase); between groups: 230 V AC (different system phase)
between channels and backplane bus/supply voltage	230 V AC
Isolation	
tested with	
• between channels and backplane bus/supply voltage	4 200 V DC/1 min, type test
• Between channels	1 500 V AC/1 min, type test
Ambient conditions	
Ambient temperature during operation	
• horizontal installation, min.	-40 °C
• horizontal installation, max.	70 °C
• vertical installation, min.	-40 °C
• vertical installation, max.	60 °C
Dimensions	
Width	22.5 mm
Height	115 mm
Depth	138 mm
Weights	
Weight, approx.	148 g
Classifications	

	Version	Classification
eClass	14	27-24-26-04
eClass	12	27-24-26-04
eClass	9.1	27-24-26-04
eClass	9	27-24-26-04

eClass	8	27-24-26-04
eClass	7.1	27-24-26-04
eClass	6	27-24-26-04
ETIM	10	EC001599
ETIM	9	EC001599
ETIM	8	EC001599
ETIM	7	EC001599

Approvals / Certificates

General Product Approval



[Miscellaneous](#)



[China RoHS](#)



General Product Approval

For use in hazardous locations



[Declaration of Conformity](#)



For use in hazardous locations

Maritime application



[Miscellaneous](#)



Maritime application

Environment



[NK / Nippon Kaiji Kyokai](#)



[CCS \(China Classification Society\)](#)



last modified:

10/23/2025