



Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.82 – 2.08 mm²**

Mating Tab Width: **5.21 mm [.205 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Insertion Force	Low
-----------------	-----

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	5.21 mm[.205 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Open

Termination Features

--	--



Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple

Dimensions

Product Length	15.62 mm[.615 in]
Compatible Insulation Diameter Range	3.3 – 4.57 mm[.13 – .179 in]
Terminal Material Thickness	.41 mm[.016 in]
Wire Size	.82 – 2.08 mm²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
---	---------

Packaging Features

Packaging Quantity	16000
Packaging Method	Strip/Reel

Other

Line	Premier
------	---------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2150084-1
OCEAN_2.0_APPLICATOR-E-100F180F-REM

TE Part # 2150084-2
OCEAN_2.0_APPLICATOR-E-100F180F-REA

TE Part # 42239-4
205 FASTON REC 18-14 AWG PHBZ

TE Part # 7-2150084-7
OCEAN_2.0_SPARE_PART_KIT-100F180F

Also in the Series | FASTON 205

Crimp Terminal Housings(3)

PCB Terminals(10)

Quick Disconnects(35)

Customers Also Bought

TE Part #63539-1
250 FASTON REC 14-10 AWG TPBR

TE Part #1-282045-2
AMP MONO-SHAPE P.C.B.CONN5P.G

TE Part #60938-2
250 FASTON REC 18-14 AWG TPBR

TE Part #62057-1
250 FASTON FLAG REC 12-10 AWG SPBZ



TE Part #63933-1
[PL .250 TERMINAL REC 22-18 AWG BR](#)

TE Part #8-1437652-2
[6PCV-05-006=6PCV ASSEMBLY](#)

TE Part #1-521204-7
[HSG, POS LOCK, .250 SERIES, 2 POSITION](#)

TE Part #AAG5872-00
[PC4D0078JR-15NY-1-ZN-L45](#)

TE Part #AAE8197-00
[PJCTNC-3-ZN-WB4-01](#)

TE Part #687392-1
[END FEED HINGE BAR APPLICATOR](#)

Documents

Product Drawings

[205 FASTON REC 18-14 AWG TPBR](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_42233-2_BJ.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_42233-2_BJ.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_42233-2_BJ.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[82004 FASTON Terminals \(Insulated and Uninsulated\) Catalog - FASTON Receptacles Section](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[UL Report](#)

42233-2

Quick Disconnect Receptacle, 18 – 14 AWG, .82 – 2.08 mm² Wire, 5.21 mm [.205 in]
Tab Width, Straight, Brass, Tin Plating, Strip/Reel, FASTON 205



English