


500 Watts

- 450-500W Forced Cooled
- 350-400W Convection Cooled
- ITE & Medical (BF) Safety Approvals
- U-Channel 4" x 7" Package
- 5V Standby & 12V Fan Supply
- AC OK, Inhibit & Remote Sense
- Class B Conducted & Radiated Emissions
- 3 Year Warranty



The PBR500 series of AC-DC switching power supplies, in a package of just 4 x 7 x 1.7 inches, deliver 450-500 watts of continuous power with forced air cooling or 350-400 watts with convection cooling. The units are constructed on a U-Channel for mechanical support and heat sinking. A cover and fan assembly can be added during manufacturing. They are designed for both ITE/Industrial and medical applications including those needing BF rated insulation with an operation altitude up to 5000 meters.

Dimensions:

PBR500:
7.0 x 4.00 x 1.70" (177.8 x 101.6 x 44.5 mm)


Models & Ratings

Output Voltage V1	Output Current V1		Standby Supply V2	Fan Supply V3	Output Power		Ripple & Noise	Model Number ⁽¹⁾
	Convection	Forced			Convection	Forced ⁽²⁾		
12 V	29.17 A	37.50 A	5.0 V / 0.5 A	12.0 V / 0.3 A	350 W	450 W	120 mV	PBR500PS12B
15 V	23.34 A	30.00 A					150 mV	PBR500PS15B
18 V	22.23 A	27.78 A					180 mV	PBR500PS18B
24 V	16.67 A	20.84 A			400 W	500 W	240 mV	PBR500PS24B
28 V	14.29 A	17.86 A					280 mV	PBR500PS28B
36 V	11.12 A	13.89 A					360 mV	PBR500PS36B
48 V	8.34 A	10.42 A					480 mV	PBR500PS48B
57 V	7.02 A	8.78 A					570 mV	PBR500PS57B

Notes

1. For covered version, replace B in the part number with C, e.g PBR500PS12C. V3 not available on covered version.
2. 350-400 W without moving air or 450-500 W with 30 CFM forced air provided by the user. 450-500 W for '-C' version
3. Ripple and noise is the maximum peak-to-peak voltage value measured at the output with 20 MHz bandwidth, at rated line voltage and output load, and with a 10 μ F tantalum capacitor in parallel with a 0.1 μ F ceramic capacitor.
4. All models may be operated at no-load without damage. At no load, output voltage fluctuates beyond 5% due to burst-mode operation of the control IC for energy saving.

Temperature Derating Curve



Input

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Input Voltage	80		264	VAC	Derate to 90% at 85 VAC & 80% at 80 VAC
Input Frequency	47		63	Hz	
Input Current - Full Load		5.2/2.6		A (rms)	115/230 VAC, 60/50 Hz
Earth Leakage Current		200	250	µA	264 VAC, 63 Hz

Output

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Output Voltage (V1)	12		57	VDC	See Models and Ratings table
Tolerance			±2	%	Line and Load Regulation, 0.1% minimum load required to meet specification
Transient Response			4	%	Recovery within 1% in less than 500 µs for a 25% step load change
Ripple & Noise			1	% pk-pk	20 MHz bandwidth, see model table notes
Overvoltage Protection	112		140	%	Latching
Overcurrent Protection	115		140	%	Trip & restart characteristic
Thermal Shutdown					Protected for overtemperature conditions
Temperature Coefficient			±0.04	%/°C	
5 V Standby Supply (V2)			5	V	At 500 mA
Fan Supply (V3)			12	V	At 300 mA
Standby Leakage Current		50	80	µA	264 VAC, 63 Hz

Environmental

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Operating Temperature	-10		+70	°C	Derate Linearly from 100% load at +50 °C to 50% load at +70 °C
Storage Temperature	-40		+85	°C	
Humidity	5		95	%RH	Non-condensing

General

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Efficiency		90		%	230 VAC, 100% load
Isolation: Input to Output Input to Ground Output to Ground	4000			VAC	2 x MOPP
	1500			VAC	1 X MOPP
	1500			VAC	1 X MOPP
Switching Frequency		85		kHz	
Hold Up Time	20			ms	At 110 VAC & 500 W
Inrush Current		30/60		VAC	115 VAC/230 VAC at 25 °C, cold start
Mean Time Between Failure		100,000		Hrs	MIL-HDBK-217F, Full load at 25 °C GB
Weight		2.23 (1011.5)		lb (g)	PBR500PSxx
		2.52 (1143.0)			PBR500PSxx-C

Signals & Controls

Characteristic	Notes & Conditions
Remote Sense	Compensates for 0.5 V total voltage drop.
Inhibit	The inhibit high pin should be pulled below 0.4 V to switch V1 & Fan Supply (V3) off. Open circuit or 2-8V maximum to switch the output on.
AC OK	TTL high for normal operation, low upon loss of input power, turn-on delay time 100-1000 ms, turn-off delay time 1 ms minimum

EMC: Emissions

Phenomenon	Standard	Test Level	Notes & Conditions
Conducted	EN55011/EN55032	Class B	
Radiated	EN55011/EN55032	Class B	
Harmonic Current	EN61000-3-2	Class A	
Voltage Fluctuations	EN61000-3-3		

EMC: Immunity


Phenomenon	Standard	Test Level	Criteria	Notes & Conditions
ESD	EN61000-4-2	4	A	±8 kV contact, ±15 kV air
Radiated	EN61000-4-3	10 V/m	A	
EFT	EN61000-4-4	±2 kV	A	
Surges	EN61000-4-5	Installation class 3	A	±1 kV differential/ ±2 kV common mode
Conducted	EN61000-4-6	10 rms	A	
Magnetic Field	EN61000-4-8	30 A/m	A	
Dips and Interruptions	400 W (100 VAC/60 Hz)	Dip 30% (70 VAC), 500ms	A	
		Dip 60% (40 VAC), 100ms	B	
		Int >95% (0 VAC), 10ms	A	
		Int 100% (0 VAC), 20ms	A	
		Int 100% (0 VAC), 5000ms	B	
	400 W (230 VAC/50 Hz)	Dip 30% (161 VAC), 500ms	A	
		Dip 60% (92 VAC), 100ms	A	
		Int >95% (0 VAC), 10ms	A	
		Int 100% (0 VAC), 20ms	A	
		Int 100% (0 VAC), 5000ms	B	
	500 W (100 VAC/60 Hz)	Dip 30% (70 VAC), 500ms	A	
		Dip 60% (40 VAC), 100ms	B	
		Int >95% (0 VAC), 10ms	A	
		Int 100% (0 VAC), 20ms	A	
		Int 100% (0 VAC), 5000ms	B	
	500 W (230 VAC/60 Hz)	Dip 30% (161 VAC), 500ms	A	
Dip 60% (92 VAC), 100ms		A		
Int >95% (0 VAC), 10ms		A		
Int 100% (0 VAC), 20ms		A		
Int 100% (0 VAC), 5000ms		B		

Safety Approvals

Safety Agency	Safety Standard	Notes & Conditions
CB Report	IEC60950-1	Information Technology
	IEC62368-1	Information Technology
	IEC60601-1 Including Risk Management	Medical
UL	ES60601-1, CSA C22.2 No.60601-1	Medical
	UL62368-1, CSA C22.2 No. 62368-1	Information Technology
TUV	EN60601-1	Medical
	EN62368-1	Information Technology

Mechanical Details

PBR500PSxx




Input Connector - P1	
Pin 1	G
Pin 2	L
Pin 3	N

Output Connector - P2	
Pin 1	V1+
Pin 2	V1 Return

P3	
Pin 1	Common Return
Pin 2	+V1 Sense
Pin 3	-V1 Sense
Pin 4	AC OK
Pin 5	Inhibit
Pin 6	+5V Standby
Pin 7	N/C
Pin 8	N/C

PBR500PSxx-C



Output Connector - P4	
Pin 1	Common Return
Pin 2	+V3

Notes

- Dimensions shown in inches [mm]
- Tolerance 0.02 [0.5] maximum
- Input connector P1 is Dinkle terminal P/N DT-35C-B01W-03, with nickel plated M3 screws.
- Output connector P2 is M4x0.7 screw connections.
- Connector P3 is Molex header 87833-08 or equivalent, mating with Molex housing 51110-0850 or equivalent.
- Fan connector P4 is JST header S2B-ZR-3.4 or equivalent, mating with JST housing ZHR-2 or equivalent.
- Weight: 1.0 Kg (2.23 lbs.) approx. for U-bracket form, 1.14 Kgs. (2.52 lbs.) approx. for enclosed form
- Maximum penetration of fixing screws is 4 mm from the outer surface of chassis.