

ME MAX 45 2-2 KMGY

Order No.: 2713706

The illustration shows the version ME MAX 45 2-2 KMGY with DIN rail connector plugged in



Electronic housing consisting of: Housing shells left and right, 2x front plate, 2x transparent cover, intermediate element, metal foot catch and spring, open housing, 32-pos. (8 x 4 pos.), width: 45 mm, color: Light gray

Commercial data

EAN	 4 017918 917463
Pack	10
Customs tariff	85369010
Gross weight in pieces	80.33 g
Country of Origin	DE
Catalog page information	Page 622 (CC-2011)

Product notes

WEEE/RoHS-compliant since:
01/04/2005



Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at <http://www.download.phoenixcontact.com>. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General

Housing type	Complete housing
Housing material	Polyamide
Color	light gray

Dimensions / positions

Length	99 mm
Constructional height	114.5 mm
Width	45 mm
Number of positions	32

Technical data

Ambient temperature (operation)	-40 °C ... 105 °C
Inflammability class according to UL 94	V0
Power dissipation at 20°C in the horizontal mounting position	8.2 W 16.5 W

Certificates



Certification

cULus Recognized, UL Recognized

Certifications applied for:

Certification Ex:

Accessories


Item	Designation	Description
------	-------------	-------------

Plug/Adapter

2908294	ME FE-CONTACT	Functional earth ground contact, for intermediate elements.
---------	---------------	---


Drawings

Drilling plan/solder pad geometry





Detailed dimensional drawing of the DIN rail connector contact pads


Explosion drawing




The illustration shows a version of the product (open housing) with accessories

Dimensioned drawing





Dimensional drawing of the ME MAX 2-2 printed circuit board, for printed circuit terminal block connection (MKDSO), view: component side



Dimensional drawing of the ME MAX 2-2 printed circuit board for plug connection (MSTBO), view: component side

Address

PHOENIX CONTACT Ltd
Halesfield 13
Telford / Shropshire / TF7 4PG,England
Phone 01952 681 700
Fax 01952 681 799
<http://www.phoenixcontact.co.uk>



Phoenix Contact Ltd.
Technical modifications reserved;