

Rittal – The System.

Faster – better – everywhere.

► Digital enclosure internal temperature display and thermostat – SK 3114.200

Date : May 27, 2017

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Digital enclosure internal temperature display and thermostat – SK 3114.200

created: 27.05.2017 build on www.rittal.com/us-en



Product description

Description: For installation in the enclosure door or wall.

Technical specifications: Three-digit, 7-segment display
Option of switching between °C/°F.
With 1800 mm long NTC sensor
Two relay outputs as change-over contact and normally open contact (max. contact load 230 V, 6 A).
Freely selectable switching difference.

Color: RAL 7035

Protection category IP to IEC 60 529: IP 54

Product features

Rated operating voltage: 100 V - 230 V, 1~, 50 Hz/60 Hz
24 V - 60 V (DC)

Installation depth: 100 mm

Temperature range: Operation (environment): +0°C...+50°C
Setting range: +5°C...+55°C

Packaging unit: 1 pc(s).

Weight/packaging unit: 0.26 kg (0.6 lb.)

EAN:	4028177631434
Customs tariff number:	90321020
ETIM 6.0:	EC002014
ETIM 5.0:	EC002014
eCl@ss 8.0/8.1:	27210707
eCl@ss 7.0/7.1:	27210707
eCl@ss 6.0/6.1:	27210707
eCl@ss 5.1/5.1.4:	27180792
Product description (long):	SK Digital temperature display and thermostat, 100-230 V, 1~, 50/60 Hz, 24-60 V (DC), Installation depth: 100 mm
Approvals	
Approvals:	UR
Certificates:	EAC
Declarations:	Declaration of conformity

2017 © Rittal Corporation